

CA-16S1N128008 - Cable connector

1619643

<https://www.phoenixcontact.com/us/products/1619643>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos.: 16, Direction of rotation: Standard, contact connection type: Socket, Solder connection, cable diameter range: 10 mm ... 14.5 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1243732

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1619643 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB31 |
| Product key | ABRAEA |
| GTIN | 4046356822350 |
| Weight per piece (including packing) | 94.5 g |
| Weight per piece (excluding packing) | 91 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

CA-16S1N128008 - Cable connector

1619643

<https://www.phoenixcontact.com/us/products/1619643>



Technical data

Product properties

| | |
|------------------------|---------------------------------|
| Product type | Circular connector (cable-side) |
| Data management status | |
| Article revision | 05 |

Connector

Connection 1

| | |
|-------------|--------|
| Head design | Socket |
|-------------|--------|

Insulating body

| | |
|------------------------------------|----------------------|
| Coding | N |
| Insulation body material | PBT |
| Contact material | CuZn |
| Contact surface material | Ni/Au |
| Insertion/withdrawal cycles | 100 |
| Connection method | Solder connection |
| Contact switching type | Socket |
| Application | Signal |
| Number of positions | 16 |
| Direction of rotation | Standard |
| Connection profile | 16 |
| Rated voltage | 48 V AC |
| | 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overshoot category | III |
| Degree of pollution | 3 |
| Contact diameter | Signal contacts |
| Litz wire cross-section | Signal contacts max. |
| Nominal current per signal contact | 1 mm ² |
| | 8 A |

Housing

| | |
|-----------------------------------|--|
| Housing material | Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn) |
| Type of locking | Screw locking mechanism |
| Pg screw connection | none |
| Degree of protection (plugged in) | IP67 |
| Thread type | M23 |

Seal

| | |
|-------------------------|-------------------|
| External cable diameter | 10 mm ... 14.5 mm |
| Seal material | NBR |

CA-16S1N128008 - Cable connector

1619643

<https://www.phoenixcontact.com/us/products/1619643>



Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

CA-16S1N128008 - Cable connector


1619643

<https://www.phoenixcontact.com/us/products/1619643>



Drawings

Schematic diagram



Connector pin assignment

CA-16S1N128008 - Cable connector

1619643

<https://www.phoenixcontact.com/us/products/1619643>



Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619643>

| cUL Recognized | | | | |
|-------------------------------|-----------------------|-----------------------|-------------------|----------------------|
| Approval ID: E335019-20141210 | | | | |
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| | 48 V | 5 A | 18 - 18 | - |

| UL Recognized | | | | |
|-------------------------------|-----------------------|-----------------------|-------------------|----------------------|
| Approval ID: E335019-20141210 | | | | |
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| | 48 V | 8 A | 18 - 18 | - |

cULus Recognized

CA-16S1N128008 - Cable connector

1619643

<https://www.phoenixcontact.com/us/products/1619643>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27440102 |
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440116 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CA-16S1N128008 - Cable connector

1619643

<https://www.phoenixcontact.com/us/products/1619643>



Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|---|---------|
| Environment friendly use period (EFUP) | EFUP-50 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. | |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | a6895255-0f7a-4aed-9aac-7e11774f0d8e |

CA-16S1N128008 - Cable connector

1619643

<https://www.phoenixcontact.com/us/products/1619643>



Accessories

SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/us/products/1607456>

Torque screwdriver, series: RC, UC, SH, SF



SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/us/products/1607455>

Hook wrench, series: RC, UC, RF, SF



CA-16S1N128008 - Cable connector

1619643

<https://www.phoenixcontact.com/us/products/1619643>



RF-Z0014 - Color coding

1620588

<https://www.phoenixcontact.com/us/products/1620588>

Color coding, color: green



RF-Z0015 - Color coding

1620592

<https://www.phoenixcontact.com/us/products/1620592>

Color coding, color: orange



CA-16S1N128008 - Cable connector



1619643

<https://www.phoenixcontact.com/us/products/1619643>

RF-Z0016 - Color coding

1620593

<https://www.phoenixcontact.com/us/products/1620593>

Color coding, color: black



RF-Z0003 - Square mounting flange

1607905

<https://www.phoenixcontact.com/us/products/1607905>

Square mounting flange, Axial seal, 4xM3, flange dimensions: 35 mm x 35 mm, series: RF, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1242369



CA-16S1N128008 - Cable connector

1619643

<https://www.phoenixcontact.com/us/products/1619643>



CA-Z0077 - Metal protective cap

1627224

<https://www.phoenixcontact.com/us/products/1627224>

Metal protective cap, degree of protection: IP67, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1245447



PROT-M23-SG-IT-IP20 - Plastic protective cap

1577206

<https://www.phoenixcontact.com/us/products/1577206>

Plastic protective cap, M23, degree of protection: IP20, series: CA, RC, RF, UC, RM



Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com