

SACC-CI-M12FS-12CON-L180 THRSH - Contact carrier



1442052

<https://www.phoenixcontact.com/us/products/1442052>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, 12-position, Socket, straight, M12, coding: A, PCB mounting, THR solder connection, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239761

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

Commercial data

| | |
|--------------------------------------|---------------------|
| Item number | 1442052 |
| Packing unit | 60 pc |
| Minimum order quantity | 60 pc |
| Sales key | AB23 |
| Product key | ABQAGG |
| Catalog page | Page 257 (C-2-2013) |
| GTIN | 4046356533126 |
| Weight per piece (including packing) | 5.47 g |
| Weight per piece (excluding packing) | 4.9 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

SACC-CI-M12FS-12CON-L180 THRSH - Contact carrier



1442052

<https://www.phoenixcontact.com/us/products/1442052>

Technical data

Notes

| | |
|--------------------|--|
| Notes on operation | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
|--------------------|--|

Product properties

| | |
|---------------------|----------------|
| Product type | Contact insert |
| Application | Signal |
| Number of positions | 12 |
| Seal present | yes |
| Shielded | yes |
| Coding | A |
| Thread type | M12 |

Data management status

| | |
|------------------|----|
| Article revision | 10 |
|------------------|----|

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|-----------------------|----------------------------|
| Rated surge voltage | 0.8 kV |
| Contact resistance | $\leq 3 \text{ m}\Omega$ |
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 30 V |
| Nominal current I_N | 1.5 A |

Connection data

| | |
|-------------------|-----------------------|
| Connection method | THR solder connection |
|-------------------|-----------------------|

Material specifications

| | |
|--|------|
| Flammability rating according to UL 94 | V0 |
| Seal material | FKM |
| Contact material | CuZn |
| Contact surface material | Au |
| Contact carrier material | PPA |

Connector

| | |
|--------------|--------|
| Connection 1 | |
| Head design | Socket |

SACC-CI-M12FS-12CON-L180 THRSH - Contact carrier



1442052

<https://www.phoenixcontact.com/us/products/1442052>

| | |
|-------------------|----------|
| Head cable outlet | straight |
| Head thread type | M12 |
| Coding | A |

Cable/line

| | |
|---------------------------------|---|
| Ambient temperature (operation) | -40 °C ... 85 °C (cable, fixed installation) |
| | -25 °C ... 85 °C (Cable, flexible installation) |

Mechanical properties

| | |
|-----------------------------|-------|
| Mechanical data | |
| Insertion/withdrawal cycles | > 100 |

Environmental and real-life conditions

| | |
|--|---|
| Ambient conditions | |
| Degree of protection (when plugged in) | IP67 (correctly plugged in and locked) |
| Degree of protection | IP67 (correctly plugged in and locked) |
| | IP67 |
| Ambient temperature (operation) | -25 °C ... 85 °C (Plug / socket) |
| | -40 °C ... 85 °C (without mechanical actuation) |
| | -25 °C ... 85 °C (Cable, flexible installation) |
| | -40 °C ... 85 °C (cable, fixed installation) |

Standards and regulations

| | |
|--------------------------|-----------------|
| M12 | |
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |

Mounting

| | |
|---------------|--------------|
| Mounting type | PCB mounting |
|---------------|--------------|

Packaging specifications

| | |
|-------------------|-------------------|
| Type of packaging | Tray |
| Delivery state | with assembly pad |

SACC-CI-M12FS-12CON-L180 THRSH - Contact carrier




1442052

<https://www.phoenixcontact.com/us/products/1442052>

Drawings

Schematic diagram



Pin assignment M12 socket, 12-pos., A-coded, view female side

SACC-CI-M12FS-12CON-L180 THRSH - Contact carrier



1442052

<https://www.phoenixcontact.com/us/products/1442052>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1442052>

| UL Recognized | | | | |
|-------------------------------|-----------------------|-----------------------|-------------------|----------------------|
| Approval ID: E118976-20100522 | | | | |
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| | 30 V | 1.5 A | 26 - 26 | - |

SACC-CI-M12FS-12CON-L180 THRSH - Contact carrier



1442052

<https://www.phoenixcontact.com/us/products/1442052>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27440223 |
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440223 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC003557 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SACC-CI-M12FS-12CON-L180 THRSH - Contact carrier



1442052

<https://www.phoenixcontact.com/us/products/1442052>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|---|---------|
| Environment friendly use period (EFUP) | EFUP-50 |
| An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. | |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | c2db21b6-e0bb-4e71-adaf-0d32b089564f |

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com