

# CA-17P1N12T006S - Cable connector



1619403

<https://www.phoenixcontact.com/us/products/1619403>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M23, Cable connector, series: CA, angled, shielded: yes, SPEEDCON, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Pin, Solder connection, cable diameter range: 4 mm ... 6 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1243521



## Your advantages

- Angled cable outlet for confined spaces
- Can be adapted to various applications, thanks to adjustable cable outlet direction
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Reduced connection time with SPEEDCON fast locking system
- Solder connection: proven connection technology for various litz wires

## Commercial data

Item number	1619403
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	AB31
Product key	ABRAED
Catalog page	Page 91 (C-2-2019)
GTIN	4046356824446
Weight per piece (including packing)	148.072 g
Weight per piece (excluding packing)	148.072 g
Customs tariff number	85366990
Country of origin	DE

# CA-17P1N12T006S - Cable connector



1619403

<https://www.phoenixcontact.com/us/products/1619403>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
Data management status	
Article revision	08

### Connector

Insulating body	
Coding	N
Insulation body material	PBT
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Pin
Application	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Contact diameter	1 mm
Litz wire cross-section	1 mm²
Nominal current per signal contact	8 A

Housing	
Housing material	Metal
Type of locking	SPEEDCON
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Seal	
External cable diameter	4 mm ... 6 mm
Seal material	NBR

### Environmental and real-life conditions

Ambient conditions
--------------------

# CA-17P1N12T006S - Cable connector



1619403

<https://www.phoenixcontact.com/us/products/1619403>

Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	15 °C ... 25 °C
Permissible humidity (storage/transport)	50 % ... 65 %

# CA-17P1N12T006S - Cable connector


1619403

<https://www.phoenixcontact.com/us/products/1619403>



## Drawings

Schematic diagram



Connector pin assignment

# CA-17P1N12T006S - Cable connector




1619403

<https://www.phoenixcontact.com/us/products/1619403>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619403>

 <b>cUL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	48 V	5 A	18 - 18	-

 <b>UL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	48 V	8 A	18 - 18	-

<b>cULus Recognized</b>				
-------------------------	--	--	--	--

# CA-17P1N12T006S - Cable connector



1619403

<https://www.phoenixcontact.com/us/products/1619403>

## Classifications

### ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CA-17P1N12T006S - Cable connector



1619403

<https://www.phoenixcontact.com/us/products/1619403>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b4e02e53-4441-4254-8cc3-cf5b3a63aacf

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)