








ADAPTER PLATE - HVP-HD1000 2POS HEADER INTERFACE



2394071-6	C	L/M	2POS,PIN DIA 10.0 HDR ASSY,90DEG	CODE HOUSING	M	PA66-GF	AQUA RED	(32S)	1	11
				CODE HOUSING	L	PA66-GF	AQUA BROWN		1	10
				FOLLOW 2394071-1	-	-	-		1	9
2394071-5	C	J/K	2POS,PIN DIA 10.0 HDR ASSY,90DEG	CODE HOUSING	K	PA66-GF	AQUA GREEN	(32S)	1	11
				CODE HOUSING	J	PA66-GF	ORANGE		1	10
				FOLLOW 2394071-1	-	-	-		-	1-9
2394071-4	C	G/H	2POS,PIN DIA 10.0 HDR ASSY,90DEG	CODE HOUSING	H	PA66-GF	YELLOW	(32S)	1	11
				CODE HOUSING	G	PA66-GF	RED		1	10
				FOLLOW 2394071-1	-	-	-		-	1-9
2394071-3	C	E/F	2POS,PIN DIA 10.0 HDR ASSY,90DEG	CODE HOUSING	F	PA66-GF	BROWN	(32S)	1	11
				CODE HOUSING	E	PA66-GF	GREEN		1	10
				FOLLOW 2394071-1	-	-	-		-	1-9
2394071-2	C	C/D	2POS,PIN DIA 10.0 HDR ASSY,90DEG	CODE HOUSING	D	PA66-GF	PURPLE	(32S)	1	11
				CODE HOUSING	C	PA66-GF	Blue		1	10
				FOLLOW 2394071-1	-	-	-		-	1-9
2394071-1	C	A/B	2POS,PIN DIA 10.0 HDR ASSY,90DEG	CODE HOUSING	B	PA66-GF	NATURE	(32S)	1	11
				CODE HOUSING	A	PA66-GF	BLACK		1	10
				HEADER TPA	-	PA66-GF	RED		2	9
				FINGER PROTECTION CAP	-	PA66	BLACK		2	8
				FACE SEAL	-	SILICONE	RED		1	7
				BUSBAR OVERMOLD,FRONT SIDE	-	-	-		2	6
				OUTER HOUSING	-	PA66-GF	BLACK		2	5
				INNER HOUSING	-	PA66-GF	BLACK		2	4
				HVIL WIRE (LEONI MOCAR 180 E 0.5SQMM, WHITE ACCORDING TO LV112) WITH TERMINAL	-	-	-		1	3
				HVIL WIRE (LEONI MOCAR 180 E 0.5SQMM, WHITE ACCORDING TO LV112) WITH TERMINAL	-	-	-		2	2
HEADER HOUSING 90DEG,2POS	-	Al-ALLOY	PASSIVATION	1	1					
TE-ASSY-NO.	TE REV.	CODE	DESCRIPTION	DESCRIPTION	CODE	MATERIAL	SURFACE COLOR /TREATMENT	WEIGHT (g)	QTY	ITEM



1. SUITABLE COUNTERPART HYP-HD1000 PLUG
SEE TE CONNECTIVITY PRODUCT DRAWING.
TE-NO.: 2394115 AND 2411905 (EMPTY)
- △ CODING VARIANT
- △ MOUNTING SPACE FOR HEADER
- △ SEALING AREA: NO BURR; TOOL PARTING, SHRINKAGE, CAVITIES AND GATE MARKS PERMITTED.
SURFACE ROUGHNESS: Ra=1.6
- △ DRAFT ANGLE UP TO 0.5° PERMITTED
- △ SCREW SCREW M5 (RECOMMENDED SCREW PLATING: ZINC-NICKEL).
SCREW TYPE UP TO MANUFACTURER
- △ MATERIAL: CORROSION RESISTANT, ELECTROCONDUCTIVE
- △ SCREW M6 FOR BUSBAR CONNECTION
- △ ALL THREAD HOLES ARE BLIND HOLES
- △ INTERFACE PANEL CODE SEE SHEET 4
POSITION NUMBER
- △ LUBRICANT APPLIED ON THE RADIAL SEAL AREA AND CPA AREA
- △ ASSEMBLY PN: X-XXXXXXX-X
DATE CODE: DWWYY

[illegible]

REVISIONS				
P	LTN	DESCRIPTION	DATE	APPD
-	-	SEE SHEET 1	-	-



TABLE 5					
*-1		*-2		*-3	
CODE A	CODE B	CODE C	CODE D	CODE E	CODE F
*-4		*-5		*-6	
CODE G	CODE H	CODE J	CODE K	CODE L	CODE M

1. MISSING DIMENSIONS FOR CODING ACC. DRAWING 2394070

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

2-PLC ±0.08

3-PLC ±0.1

4-PLC ±0.0001

FINISH

APPROVALS:

DESIGNER

CHK

APPD

DATE

WEIGHT

SEE TABLE

CUSTOMER DRAWING

DATE

26AUG2021

DATE

26AUG2021

DATE

26AUG2021

PRODUCT SPEC

108-160341

APPLICATION SPEC

114-160181

WEIGHT

SEE TABLE

CUSTOMER DRAWING

NAME

2PDS.PIN DIA 10.0 HDR ASSY.90DEG

HVP-HD1000

SIZE

00779

CASE CODE

C=2394071

RESTRICTED TO

-

REV

C

SCALE

2:1

SHEET

6

OF

6

REV

C

TE Connectivity