

IPD WD 3P2,5 M20 GY - Panel feed-through



1047319

<https://www.phoenixcontact.com/us/products/1047319>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel feed-through, Direct connection, product family: IPD, connection method: Push-in connection/ Push-in connection, number of positions: 2+PE, M20, 0.5 mm² ... 2.5 mm², 600 V, 20 A, PA, light gray, external cable diameter: 6 mm ... 9 mm and 8 mm ... 13 mm

Your advantages

- Convenient: quick and easy assembly without special tools
- Fast and easy startup, thanks to tool-free Push-in connection technology
- Reliable installation in harsh environments with IP66, IP68, and IP69K throughout the entire system

Commercial data

Item number	1047319
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF51
Product key	BF6IAA
Catalog page	Page 468 (C-2-2019)
GTIN	4055626648200
Weight per piece (including packing)	55.5 g
Weight per piece (excluding packing)	54 g
Customs tariff number	85366990
Country of origin	CN

IPD WD 3P2,5 M20 GY - Panel feed-through



1047319

<https://www.phoenixcontact.com/us/products/1047319>

Technical data

Product properties

Product type	Panel feed-through
Product family	IPD
Number of positions	3
Connection profile	2+PE
Position marking	L, N, PE
Type	Direct connection

Data management status

Article revision	03
------------------	----

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Connection data


Connection technology

Connection method On the device side	Push-in connection
Connection method On the field side	Push-in connection
Frequency of connections between conductors of the same cross section	max. 10

Conductor connection

Conductor cross section flexibel	0.5 mm ² ... 2.5 mm ²
Conductor cross section solid	0.5 mm ² ... 2.5 mm ²
Conductor cross section with ferrule	0.5 mm ² ... 2.5 mm ²
Connection cross section AWG	20 ... 14

Dimensions

Dimensional drawing	
Width	28.6 mm
Length	90.8 mm

Electrical properties

Rated surge voltage (III/3)	6 kV
Rated current	20 A
Rated voltage (III/3)	600 V
Nominal voltage U _N	690 V AC 690 V DC

IPD WD 3P2,5 M20 GY - Panel feed-through



1047319

<https://www.phoenixcontact.com/us/products/1047319>

Nominal current I_N	20 A (observe derating)
-----------------------	-------------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	10
-----------------------------	----

Material specifications

Color	light gray (RAL 7035)
Material Housing	PA
Material Seal	NBR (Field)
	EPDM (Device)
Flammability rating according to UL 94	V0
Contact material	Cu
Contact surface material	Ni/Sn

Cable/line

External cable diameter	6 mm ... 9 mm
	8 mm ... 13 mm
Stripping length of the individual wire	10 mm
Position marking	L, N, PE

Mounting


Mounting type	Front mounting M20
---------------	--------------------

Environmental and real-life conditions


Ambient conditions

Degree of protection	IP66
	IP68 (2 m / 24 h)
	IP69K
Impact strength	IK07
Ambient temperature (operation)	-40 °C ... 100 °C (T = 55 °C)
Temperature when conductor connected	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-40 °C ... 100 °C
Resistance to UV radiation	yes


Drawings




Derating diagram for 1.0 mm²



Derating diagram for 1.5 mm²



Derating diagram for 2.5 mm²



IPD WD 3P2,5 M20 GY - Panel feed-through



1047319

<https://www.phoenixcontact.com/us/products/1047319>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1047319>



VDE Zeichengenehmigung

Approval ID: 40049992

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	690 V	20 A	-	0.5 - 2.5

DNV

Approval ID: TAE00004G2



UL Listed

Approval ID: E468743

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Only rigid conductors	600 V	20 A	-	- 14
multi-stranded with ferrule	600 V	20 A	-	- 14



cUL Listed

Approval ID: E468743

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	600 V	17 A	- 14	-

cULus Listed

IPD WD 3P2,5 M20 GY - Panel feed-through



1047319

<https://www.phoenixcontact.com/us/products/1047319>

Classifications

ECLASS

ECLASS-11.0	27440602
ECLASS-12.0	27440602
ECLASS-13.0	27440602

ETIM

ETIM 9.0	EC002566
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%