

# FLKM-KS40/YCS - Passive module



2314642

<https://www.phoenixcontact.com/us/products/2314642>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Universal interface module with 1:1 connection between the 40-pos. system connection and the screw connection.

## Your advantages

- For analog modules
- Universal interface module with 40 connection terminal blocks

## Commercial data

Item number	2314642
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C421
Product key	CK218N
Catalog page	Page 520 (C-5-2017)
GTIN	4046356147057
Weight per piece (including packing)	247.3 g
Weight per piece (excluding packing)	176.9 g
Customs tariff number	85369010
Country of origin	DE

# FLKM-KS40/YCS - Passive module

2314642

<https://www.phoenixcontact.com/us/products/2314642>



## Technical data

### Product properties

Product type	Interface module
No. of channels	4
	8
	12
	16
Operating mode	100% operating factor

### Data management status

Article revision	05
------------------	----

### Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

### Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 30 V DC
Current (per branch)	≤ 1 A

### Air clearances and creepage distances

Rated insulation voltage	50 V
Rated surge voltage	0.5 kV (1.2/50 µs)

### Supported controller YOKOGAWA CS3000 CentumVP

Suitable I/O card	AAB841
	AAI135
	AAI141
	AAI143
	AAI543
	AAI835
	AAI841
	AAR181
	AAT141
	AAV141
	AAV142
	AAV542
	AAP135

### Supported controller YOKOGAWA STARDOM

Suitable I/O card	NFAI141
	NFAI43

# FLKM-KS40/YCS - Passive module

2314642

<https://www.phoenixcontact.com/us/products/2314642>



NFAI543
NFAI135
NFAP135
NFAV141
NFAV142
NFAV542
NFAB841
NFAI841
NFAI835

## Connection data

### Connection 1 (control level)

Connection method	Yokogawa KS-compatible
Number of connections	1
Number of positions	40
Note	Usable system cables: Phoenix Contact YUC40, Yokogawa KS1
Tightening torque	0.5 Nm
Pitch	2.54 mm

### Connection 2 (field level)

Connection method	Screw connection
Stripping length	7 mm
Screw thread	M3
Number of positions	40
Conductor cross section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section rigid (2 conductors with same cross section)	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> 0.25 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule without plastic sleeve) 0.25 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (Ferrule with plastic sleeve)
Conductor cross section flexible (2 conductors with same cross section)	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> 0.25 mm <sup>2</sup> ... 0.75 mm <sup>2</sup> (Ferrule without plastic sleeve) 0.5 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> (TWIN ferrule with plastic sleeve)
Conductor cross section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm
Pitch	5.08 mm

## Signaling

Status display present	No
------------------------	----

## Dimensions

Item dimensions
Width
Height

# FLKM-KS40/YCS - Passive module

2314642

<https://www.phoenixcontact.com/us/products/2314642>



Depth	65.8 mm
-------	---------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (Module)	IP00
Degree of protection (Installation location)	≤ IP54
Ambient temperature (operation)	-20 °C ... 65 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Altitude	≤ 2000 m

## Approvals

### UKCA

Certificate	UKCA-compliant
-------------	----------------

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	EN IEC 60664-1
-----------------------	----------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

# FLKM-KS40/YCS - Passive module


2314642

<https://www.phoenixcontact.com/us/products/2314642>



## Drawings

Circuit diagram




# FLKM-KS40/YCS - Passive module



2314642

<https://www.phoenixcontact.com/us/products/2314642>

Dimensional drawing



# FLKM-KS40/YCS - Passive module

2314642

<https://www.phoenixcontact.com/us/products/2314642>



## Classifications

### ECLASS

ECLASS-11.0	27141152
ECLASS-12.0	27141152
ECLASS-13.0	27141152

### ETIM

ETIM 9.0	EC002780
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FLKM-KS40/YCS - Passive module

2314642

<https://www.phoenixcontact.com/us/products/2314642>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)