

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Contact carrier, Power, 4-position, Socket, straight, M12, coding: T, PCB mounting, SMD reflow



Your advantages

- For compact devices: transmit high power in a confined space
- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

Commercial data

Item number	1411967
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	AB23
Product key	ABQBGI
GTIN	4046356991643
Weight per piece (including packing)	3.769 g
Weight per piece (excluding packing)	3.769 g
Customs tariff number	85366990
Country of origin	DE

SACC-CI-M12FST-4P SMD SH T - Contact carrier

1411967

<https://www.phoenixcontact.com/us/products/1411967>



Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Power
Sensor type	Power
Number of positions	4
Seal present	no
Shielded	yes
Coding	T
Thread type	M12

Data management status

Article revision	02
------------------	----

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	1.5 kV
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Nominal voltage U _N	63 V
Nominal current I _N	12 A

Connection data

Connection method	SMD reflow
-------------------	------------

Interfaces

Signal type/category	Power
----------------------	-------

Material specifications

Flammability rating according to UL 94	V0
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA

SACC-CI-M12FST-4P SMD SH T - Contact carrier

1411967

<https://www.phoenixcontact.com/us/products/1411967>



Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	T

Cable/line

Signal type/category	Power
----------------------	-------

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	> 100

Environmental and real-life conditions

Ambient conditions	
Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when plugged in
Ambient temperature (operation)	-25 °C ... 105 °C (Plug / socket)
	-55 °C ... 105 °C (without mechanical actuation)

Standards and regulations

M12	
Standard designation	M12 connector
Standards/specifications	IEC 61076-2-111
Note	In line with

Mounting

Mounting type	PCB mounting
---------------	--------------

Packaging specifications

Type of packaging	Tray
-------------------	------

SACC-CI-M12FST-4P SMD SH T - Contact carrier


1411967

<https://www.phoenixcontact.com/us/products/1411967>



Drawings

Schematic diagram



Pin assignment of M12 socket, 4-pos., T-coded, socket side view

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1411967>

cUL Recognized			
Approval ID: E468743-20190917			
Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
63 V	8 A	-	-

UL Recognized			
Approval ID: E468743-20190917			
Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
63 V	10 A	-	-

cULus Recognized

SACC-CI-M12FST-4P SMD SH T - Contact carrier

1411967

<https://www.phoenixcontact.com/us/products/1411967>



Classifications

ECLASS

ECLASS-11.0	27440110
ECLASS-12.0	27440110
ECLASS-13.0	27440110

ETIM

ETIM 9.0	EC003568
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CI-M12FST-4P SMD SH T - Contact carrier

1411967

<https://www.phoenixcontact.com/us/products/1411967>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	e3679848-2733-4a98-9037-e37cdfb7b12c

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com