

# PTSM 0,5/ 6-2,5-V SMD WH R44 - PCB terminal block



1814744

<https://www.phoenixcontact.com/us/products/1814744>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB terminal block, nominal current: 6 A, rated voltage (III/2): 160 V, nominal cross section: 0.5 mm<sup>2</sup>, number of potentials: 6, number of rows: 1, number of positions per row: 6, product range: PTSM 0,5/..-V-SMD WH, pitch: 2.5 mm, connection method: Push-in spring connection, mounting: SMD soldering, conductor/PCB connection direction: 90 °, color: signal white, Pin layout: Linear pad geometry, Solder pin [P]: 2 mm, number of solder pins per potential: 1, type of packaging: 44 mm wide tape

## Your advantages

- White design: Stable color when welding and during use
- Time saving push-in connection, tools not required
- Defined contact force ensures that contact remains stable over the long term
- High current carrying capacity of 6 A in very compact dimensions
- Designed for integration into the SMT soldering process
- Vertical connection enables multi-row arrangement on the PCB
- Additional solder anchors reduce the mechanical strain on the soldering spots

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1814744                        |
| Packing unit                         | 400 pc                         |
| Minimum order quantity               | 400 pc                         |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AA11                           |
| Product key                          | AAKDAD                         |
| Catalog page                         | Page 393 (C-1-2013)            |
| GTIN                                 | 4046356760492                  |
| Weight per piece (including packing) | 2.912 g                        |
| Weight per piece (excluding packing) | 2.3 g                          |
| Customs tariff number                | 85369010                       |
| Country of origin                    | IN                             |

1814744

<https://www.phoenixcontact.com/us/products/1814744>

## Technical data

### Product properties

|                           |                                |
|---------------------------|--------------------------------|
| Product type              | Printed circuit board terminal |
| Product family            | PTSM 0,5/...-V-SMD WH          |
| Product line              | COMBICON Terminals XS          |
| Number of positions       | 6                              |
| Pitch                     | 2.5 mm                         |
| Number of connections     | 6                              |
| Number of rows            | 1                              |
| Number of potentials      | 6                              |
| Pin layout                | Linear pad geometry            |
| Solder pins per potential | 1                              |

### Data management status

|                  |    |
|------------------|----|
| Article revision | 00 |
|------------------|----|

### Electrical properties

|                             |        |
|-----------------------------|--------|
| Nominal current $I_N$       | 6 A    |
| Nominal voltage $U_N$       | 160 V  |
| Rated voltage (III/3)       | 63 V   |
| Rated surge voltage (III/3) | 2.5 kV |
| Rated voltage (III/2)       | 160 V  |
| Rated surge voltage (III/2) | 2.5 kV |
| Rated voltage (II/2)        | 320 V  |
| Rated surge voltage (II/2)  | 2.5 kV |

### Connection data

#### Connection technology

|                       |                     |
|-----------------------|---------------------|
| Nominal cross section | 0.5 mm <sup>2</sup> |
|-----------------------|---------------------|

#### Conductor connection

|                                                                       |                                                                                                                                                                          |
|-----------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Connection method                                                     | Push-in spring connection                                                                                                                                                |
| Conductor cross section rigid                                         | 0.14 mm <sup>2</sup> ... 0.5 mm <sup>2</sup>                                                                                                                             |
| Conductor cross section flexible                                      | 0.2 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> (up to 0.75 mm <sup>2</sup> supported, with a stripping length of 7.5 mm and a rated insulation voltage of 32 V at III/2)    |
| Conductor cross section AWG                                           | 26 ... 20                                                                                                                                                                |
| Conductor cross section flexible, with ferrule without plastic sleeve | 0.25 mm <sup>2</sup> ... 0.5 mm <sup>2</sup>                                                                                                                             |
| Conductor cross section, flexible, with ferrule, with plastic sleeve  | 0.25 mm <sup>2</sup> ... 0.34 mm <sup>2</sup> (possible from 0.14 mm <sup>2</sup> , when using ferrule AI 0.14- 6 GY in combination with crimping pliers CRIMPFOX 10T-F) |
| Cylindrical gauge a x b / diameter                                    | - / 1.2 mm                                                                                                                                                               |
| Stripping length                                                      | 6 mm                                                                                                                                                                     |

1814744

<https://www.phoenixcontact.com/us/products/1814744>

## Mounting

|               |                     |
|---------------|---------------------|
| Mounting type | SMD soldering       |
| Pin layout    | Linear pad geometry |

### Processing notes

|                                           |                  |
|-------------------------------------------|------------------|
| Process                                   | Reflow soldering |
| Moisture Sensitive Level                  | MSL 1            |
| Classification temperature T <sub>c</sub> | 260 °C           |
| Solder cycles in the reflow               | 3                |

## Material specifications

### Material data - contact

|                                          |                                                                                  |
|------------------------------------------|----------------------------------------------------------------------------------|
| Note                                     | WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201 |
| Contact material                         | Cu alloy                                                                         |
| Surface characteristics                  | hot-dip tin-plated                                                               |
| Metal surface terminal point (top layer) | Tin (4 - 8 µm Sn)                                                                |
| Metal surface soldering area (top layer) | Tin (4 - 8 µm Sn)                                                                |

### Material data - housing

|                                        |                     |
|----------------------------------------|---------------------|
| Color (Housing)                        | signal white (9003) |
| Insulating material                    | PA GF               |
| Insulating material group              | I                   |
| CTI according to IEC 60112             | 600                 |
| Flammability rating according to UL 94 | V0                  |


### Material data – actuating element

|                           |              |
|---------------------------|--------------|
| Color (Actuating element) | white (9010) |
|---------------------------|--------------|

## Notes

|                     |                                                                                                                                               |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Note on application | Pick and place pads may protrude beyond the components. The PCB layout must ensure that collisions are avoided when components are assembled. |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|

## Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Pitch               | 2.5 mm                                                                               |
| Width [w]           | 20.1 mm                                                                              |
| Height [h]          | 9 mm                                                                                 |
| Length [l]          | 7 mm                                                                                 |
| Installed height    | 9 mm                                                                                 |

|                       |      |
|-----------------------|------|
| Solder pin length [P] | 2 mm |
|-----------------------|------|

## PCB design

|              |              |
|--------------|--------------|
| Pad geometry | 1.4 x 3.4 mm |
| Pin spacing  | 2.5 mm       |

## Mechanical tests

## Connection test

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60998-2-2:2002-12 |
| Result        | Test passed           |

## Test for conductor damage and slackening

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60998-2-2:2002-12 |
| Result        | Test passed           |

## Pull-out test

|                                                                             |                                          |
|-----------------------------------------------------------------------------|------------------------------------------|
| Specification                                                               | IEC 60998-2-2:2002-12                    |
| Conductor cross section/conductor type/tractive force setpoint/actual value | 0.14 mm <sup>2</sup> / solid / > 10 N    |
|                                                                             | 0.2 mm <sup>2</sup> / flexible / > 10 N  |
|                                                                             | 0.5 mm <sup>2</sup> / solid / > 20 N     |
|                                                                             | 0.75 mm <sup>2</sup> / flexible / > 30 N |

## Flexion test

|               |                       |
|---------------|-----------------------|
| Specification | IEC 60998-2-2:2002-12 |
| Result        | Test passed           |

## Electrical tests

## Temperature-rise test

|                                   |                                |
|-----------------------------------|--------------------------------|
| Specification                     | IEC 60998-2-1:2002-12          |
| Requirement temperature-rise test | Increase in temperature ≤ 45 K |

## Insulation resistance

|                                              |                     |
|----------------------------------------------|---------------------|
| Specification                                | IEC 60998-1:2002-12 |
| Insulation resistance, neighboring positions | > 5 MΩ              |

## Air clearances and creepage distances |

|                                                        |                     |
|--------------------------------------------------------|---------------------|
| Specification                                          | IEC 60664-1:2007-04 |
| Insulating material group                              | I                   |
| Comparative tracking index (IEC 60112)                 | CTI 600             |
| Rated insulation voltage (III/3)                       | 63 V                |
| Rated surge voltage (III/3)                            | 2.5 kV              |
| minimum clearance value - non-homogenous field (III/3) | 1.5 mm              |
| minimum creepage distance (III/3)                      | 1.6 mm              |
| Rated insulation voltage (III/2)                       | 160 V               |
| Rated surge voltage (III/2)                            | 2.5 kV              |
| minimum clearance value - non-homogenous field (III/2) | 1.5 mm              |

# PTSM 0,5/ 6-2,5-V SMD WH R44 - PCB terminal block



1814744

<https://www.phoenixcontact.com/us/products/1814744>

|                                                       |        |
|-------------------------------------------------------|--------|
| minimum creepage distance (III/2)                     | 1.5 mm |
| Rated insulation voltage (II/2)                       | 320 V  |
| Rated surge voltage (II/2)                            | 2.5 kV |
| minimum clearance value - non-homogenous field (II/2) | 1.5 mm |
| minimum creepage distance (II/2)                      | 1.6 mm |

## Environmental and real-life conditions

### Vibration test

|                        |                             |
|------------------------|-----------------------------|
| Specification          | IEC 60068-2-6:2007-12       |
| Frequency              | 10 - 150 - 10 Hz            |
| Sweep speed            | 1 octave/min                |
| Amplitude              | 0.35 mm (10 Hz ... 60.1 Hz) |
| Acceleration           | 5g (60.1 Hz ... 150 Hz)     |
| Test duration per axis | 2.5 h                       |
| Test directions        | X-, Y- and Z-axis           |


### Glow-wire test

|                  |                     |
|------------------|---------------------|
| Specification    | IEC 60998-1:2002-12 |
| Temperature      | 850 °C              |
| Time of exposure | 5 s                 |

### Ambient conditions


|                                         |                                                                               |
|-----------------------------------------|-------------------------------------------------------------------------------|
| Ambient temperature (operation)         | -40 °C ... 100 °C (Depending on the current carrying capacity/derating curve) |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C                                                              |
| Relative humidity (storage/transport)   | 30 % ... 70 %                                                                 |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                                              |

## Packaging specifications

|                             |                                                                                      |
|-----------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing         |  |
| Type of packaging           | 44 mm wide tape                                                                      |
| [W] tape width              | 44 mm                                                                                |
| [W2] coil overall dimension | 50.4 mm                                                                              |
| [A] coil diameter           | 330 mm                                                                               |
| Outer packaging type        | Transparent-Bag                                                                      |
| ESD level                   | (D) electrostatically conductive                                                     |
| Specification               | DIN EN 61340-5-1 (VDE 0300-5-1): 2008-07                                             |


## Drawings

Drilling plan/solder pad geometry



Dimension M: 18.4 mm

Diagram




Type: PTSM 0,5/...-2,5-V SMD WH R44  
 Tested in accordance with DIN EN 60512-5-2:2003-01  
 Reduction factor = 1  
 Number of positions: 5

1814744

<https://www.phoenixcontact.com/us/products/1814744>

Dimensional drawing



# PTSM 0,5/ 6-2,5-V SMD WH R44 - PCB terminal block



1814744

<https://www.phoenixcontact.com/us/products/1814744>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1814744>

|  <b>UL Recognized</b><br>Approval ID: E118976-20130619 |                       |                       |                   |                             |
|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                         | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B                                                                                                                             |                       |                       |                   |                             |
|                                                                                                                                         | 150 V                 | 5 A                   | 26 - 18           | -                           |

|  <b>cULus Recognized</b><br>Approval ID: E60425-20030527 |                       |                       |                   |                             |
|-------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                           | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| Use group B                                                                                                                               |                       |                       |                   |                             |
|                                                                                                                                           | 150 V                 | 5 A                   | 26 - 20           | -                           |

|  <b>VDE Zeichengenehmigung</b><br>Approval ID: 40048725 |                       |                       |                   |                             |
|--------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
|                                                                                                                                            | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|                                                                                                                                            | 160 V                 | 6 A                   | -                 | 0.14 - 0.5                  |

# PTSM 0,5/ 6-2,5-V SMD WH R44 - PCB terminal block



1814744

<https://www.phoenixcontact.com/us/products/1814744>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27460101 |
| ECLASS-12.0 | 27460101 |
| ECLASS-13.0 | 27460101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002643 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PTSM 0,5/ 6-2,5-V SMD WH R44 - PCB terminal block



1814744

<https://www.phoenixcontact.com/us/products/1814744>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)