

PSM-SET-SC-DUPLEX/2-HCS/PN - FO connectors



2313779

<https://www.phoenixcontact.com/us/products/2313779>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

FO connectors, degree of protection: IP20, number of positions: 2, MM, cable outlet: straight



Your advantages

- Suitable for quick and easy field assembly or repair
- Flexible application, thanks to reusable connector
- Outstanding transmission properties
- Ideal for PCF graded-index (GI) fibers
- Compact design, thanks to SC duplex pin connector pattern
- No bonding or polishing

Commercial data

Item number	2313779
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIAB
Catalog page	Page 377 (C-2-2019)
GTIN	4046356572965
Weight per piece (including packing)	35.8 g
Weight per piece (excluding packing)	35.8 g
Customs tariff number	85367000
Country of origin	DE

Technical data

Product properties

Product type	Data connector (cable side)
Type	SC-RJ
Number of positions	2
Cable outlet	straight

Data management status

Article revision	05
------------------	----

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Attenuation	≥ 2 dB (Insertion attenuation)
Transmission medium	FO
Transmission characteristics (category)	MM

Dimensions

Width	25 mm
Height	10 mm
Length	88.5 mm

Material specifications

Flammability rating according to UL 94	V0
--	----

Cable/line

Cable type	for all common PCF cable types
External cable diameter	2.2 mm ... 2.2 mm
Individual wire diameter	2.2 mm

FO cable

Number of fibers	2
Fiber type	PCF
Attenuation	≤ 1.5 dB
Transmission medium	FO

Characteristics

Attenuation	≥ 2 dB (Insertion attenuation)
-------------	-------------------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
----------------------	------

PSM-SET-SC-DUPLEX/2-HCS/PN - FO connectors



2313779

<https://www.phoenixcontact.com/us/products/2313779>

Ambient temperature (operation)	-25 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (assembly)	0 °C ... 50 °C

Classifications

ECLASS

ECLASS-11.0	19170122
ECLASS-12.0	19170122
ECLASS-13.0	19170122

ETIM

ETIM 9.0	EC001122
----------	----------

UNSPSC

UNSPSC 21.0	43223300
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com