




Part Number : [878580002](#)
Product Description : 2.00mm Pitch Milli-Grid Breakaway Header, Surface Mount, Single Row, Parallel, with Peg, without Pick-and-Place Polyimide Tape, Tray Packaging, Mating Pin Length 3.20mm , 2 Circuits, Lead-Free
Series Number : 87858
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources


Drawings
[878580002_sd.pdf](#)
[PK-87858-300-000.pdf](#)
[PK-89990-487-001.pdf](#)

3D Models and Design Files
[878580002_stp.zip](#)

Specifications
[503940001-AS-000.pdf](#)
[PS-87761-100-001.pdf](#)
[877610000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	87858
Description	2.00mm Pitch Milli-Grid Breakaway Header, Surface Mount, Single Row, Parallel, with Peg, without Pick-and-Place Polyimide Tape, Tray Packaging, Mating Pin Length 3.20mm , 2 Circuits, Lead-Free
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Family	Milli-Grid Connector System
Product Name	Milli-Grid
UPC	822348235841

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V

Physical

Breakaway	Yes
Circuits (Loaded)	2
Circuits (maximum)	2

Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	3.20mm
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.059/g
Number of Rows	1
Orientation	Parallel
Packaging Type	Tray
PC Tail Length	2.80mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	2.540µm
Polarized to Mating Part	No
Polarized to PCB	Yes
Shrouded	No
Stackable	No
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Surface Mount

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	2.00mm Single Row Receptacles