



广东容硕半导体有限公司

Guangdong Roso Semiconductor Co.,Ltd

系列规格书

系列类型：高频低阻 **RVE**

产品名称：贴片铝电解电容器

APPROVAL		
APPROVAL	CHECK	PREPARE
技术部 陈小英	副 总 黄 杰	总 经 理 徐永康

公司电话：0752-6633993

公司网址：WWW.GDRSDR.COM

公司邮箱：SALES-1@GDRSDR.COM

公司地址：广东省惠州市博罗县泰美镇泰良路8号


貼片鋁電解電容器代碼標志

Code Sign SMD(V-Chip) Aluminum Electrolytic Capacitor

代碼解釋 Explanation of Part Number

1 2 3	產品型號 Series	RVS		RVK		RVT		RVE		RVW		RVH		RVN		RVZ		RVL			
4 5	額定電壓 R.W.Voltage(V)	4		6.3		10		16		25		35		50		63		100		400	
	代號 Code	0G		0J		1A		1C		1E		1V		1H		2J		2A		2G	
6 7 8	標稱容量 Capacitance(uf)	1	2.2	3.3	4.7	6.8	8.2	10	22	33	47	100	150	220	330	470	680	1000	1500		
	代號 Code	1R0	2R2	3R3	4R7	6R8	8R2	100	220	330	470	100	151	221	331	471	681	102	152		
9	容量允許誤差 Cap. Tol	±5%			±10%			±20%			0~20%			-10~30%			-10~20%				
	代號 Code	J			K			M			A			Q			V				
10 11 12 13	尺寸 Size	4×5.4		5×5.4		6.3×5.4		6.3×7.7		8×6.5		8×10.2		10×10.2		8×12		10×12			
	代號 Code	0405		0505		0605		0607		0806		0810		1010		0812		1012			

實例 For Example: RVE 100μF 10V



RVE Series




- A. 适用于回流焊
Reflow soldering available for reflow soldering.
- B. 适用于高密度表面组装
Available for high density surface mounting.
- C. 低阻抗品
low impedance
- D. 寿命: 105℃, 2000小时
Lifetime: 105℃, 2000Hr long life product
- E. ROHS. REACH指令已对应完畢
Adapted to the ROHS. REACH directive.

主要技術性能 Specifications

使用溫度範圍 Operating temperature range	-55~+105℃																											
額定電壓範圍 Rated voltage range	6.3V~50V DC																											
標稱電容量範圍 Nominal capacitance range	1~1500 μ F																											
標稱電容量允許偏差 Nominal capacitance tolerance	± 20% (120Hz, 20℃)																											
漏電流(20℃) Leakage current	$I \leq 0.01CV$ (μA) 或3 μA取較大者(2分鐘) Less than 0.01CV(μA) or 3 μA whichever is greater (after 2 minutes)																											
損耗角正切值 Dissipation factor (120Hz 20℃)	<table><tr><th>Rated Voltage(V)</th><th>6.3</th><th>10</th><th>16</th><th>25</th><th>35</th><th>50</th></tr><tr><td>Tan δ (max)</td><td>0.26</td><td>0.20</td><td>0.16</td><td>0.14</td><td>0.12</td><td>0.12</td></tr></table>							Rated Voltage(V)	6.3	10	16	25	35	50	Tan δ (max)	0.26	0.20	0.16	0.14	0.12	0.12							
Rated Voltage(V)	6.3	10	16	25	35	50																						
Tan δ (max)	0.26	0.20	0.16	0.14	0.12	0.12																						
溫度特性(120Hz) Temperature characteristics impedance ratio(120Hz)	<table><tr><th>Rated Voltage(V)</th><th>6.3</th><th>10</th><th>16</th><th>25</th><th>35</th><th>50</th></tr><tr><td>Z-25℃/Z+20℃</td><td>4</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td></tr><tr><td>Z-55℃/Z+20℃</td><td>12</td><td>8</td><td>6</td><td>4</td><td>3</td><td>3</td></tr></table>							Rated Voltage(V)	6.3	10	16	25	35	50	Z-25℃/Z+20℃	4	3	2	2	2	2	Z-55℃/Z+20℃	12	8	6	4	3	3
Rated Voltage(V)	6.3	10	16	25	35	50																						
Z-25℃/Z+20℃	4	3	2	2	2	2																						
Z-55℃/Z+20℃	12	8	6	4	3	3																						
耐久性 Load life	+105℃施加額定電壓2000小時，恢復16小時後，電容器應滿足下要求 After applying rated voltage for 2000 hours at +105℃ and then resumed 16 hours, the capacitor shall meet the following limits. <table><tr><td>電容量變化率 Capacitance change</td><td>≤ ± 30%初始值以內 ≤ ± 30% of initial measured value</td></tr><tr><td>漏電流值 Leakage</td><td>≤ 初始規定值 ≤ Initial specified value</td></tr><tr><td>損耗角正切值 Dissipation factor</td><td>≤ 300%初始規定值 ≤ 300% of initial specified value</td></tr></table>							電容量變化率 Capacitance change	≤ ± 30%初始值以內 ≤ ± 30% of initial measured value	漏電流值 Leakage	≤ 初始規定值 ≤ Initial specified value	損耗角正切值 Dissipation factor	≤ 300%初始規定值 ≤ 300% of initial specified value															
電容量變化率 Capacitance change	≤ ± 30%初始值以內 ≤ ± 30% of initial measured value																											
漏電流值 Leakage	≤ 初始規定值 ≤ Initial specified value																											
損耗角正切值 Dissipation factor	≤ 300%初始規定值 ≤ 300% of initial specified value																											
高溫儲存 Shelf life	+105℃, 1000小時，恢復16小時，電容器應滿足下要求 After storage for 1000 hours at +105℃ and resumed 16 hours, the capacitor shall meet the following limits. <table><tr><td>電容量變化率 Capacitance change</td><td>≤ ± 30%初始值以內 ≤ ± 30% of initial measured value</td></tr><tr><td>漏電流值 Leakage</td><td>≤ 2倍初始規定值 ≤ 200% of initial specified value</td></tr><tr><td>損耗角正切值 Dissipation factor</td><td>≤ 300%初始規定值 ≤ 300% of initial specified value</td></tr></table>							電容量變化率 Capacitance change	≤ ± 30%初始值以內 ≤ ± 30% of initial measured value	漏電流值 Leakage	≤ 2倍初始規定值 ≤ 200% of initial specified value	損耗角正切值 Dissipation factor	≤ 300%初始規定值 ≤ 300% of initial specified value															
電容量變化率 Capacitance change	≤ ± 30%初始值以內 ≤ ± 30% of initial measured value																											
漏電流值 Leakage	≤ 2倍初始規定值 ≤ 200% of initial specified value																											
損耗角正切值 Dissipation factor	≤ 300%初始規定值 ≤ 300% of initial specified value																											
耐熱性 Resistance to soldering heat	在250℃的條件下，電容器應在熱板上保持30秒，然後從熱板上取出電容器，讓其在溫室下恢復，電容器應滿足以下要求。 The capacitors shall be kept on the hot plate maintained at 250℃ for 30 seconds. After removing from the hot plate and restored at room temperature, then meet the following requirement. <table><tr><td>電容量變化率 Capacitance change</td><td>≤ ± 10%初始值以內 ≤ ± 10% of initial measured value</td></tr><tr><td>漏電流值 Leakage</td><td>≤ 初始規定值 ≤ Initial specified value</td></tr><tr><td>損耗角正切值 Dissipation factor</td><td>≤ 初始規定值 ≤ Initial specified value</td></tr></table>							電容量變化率 Capacitance change	≤ ± 10%初始值以內 ≤ ± 10% of initial measured value	漏電流值 Leakage	≤ 初始規定值 ≤ Initial specified value	損耗角正切值 Dissipation factor	≤ 初始規定值 ≤ Initial specified value															
電容量變化率 Capacitance change	≤ ± 10%初始值以內 ≤ ± 10% of initial measured value																											
漏電流值 Leakage	≤ 初始規定值 ≤ Initial specified value																											
損耗角正切值 Dissipation factor	≤ 初始規定值 ≤ Initial specified value																											

■ 尺寸及印字 Dimensions & Marking



ΦD	A	B	C	P	L	H	mm
4.0	4.3	4.3	5.0	1.0	5.4	0.5~0.8	
5.0	5.3	5.3	6.0	1.5	5.4	0.5~0.8	
6.3	6.6	6.6	7.2	2.1	5.4	0.5~0.8	
8.0	8.3	8.3	9.1	3.1	10.2	0.8~1.1	
10.0	10.3	10.3	11.1	4.5	10.2	0.8~1.1	

■ 標稱電容量、額定電壓、額定紋波電流與外形尺寸對應表 Nominal capacitance, rated voltage, rated ripple current and case size table

WV	6.3V			10V			16V			25V			35V			50V		
uF	D×Lmm	Z	mA	D×Lmm	Z	mA	D×Lmm	Z	mA	D×Lmm	Z	mA	D×Lmm	Z	mA	D×Lmm	Z	mA
1																4*5.4	5.0	30
2.2																4*5.4	5.0	30
3.3																4*5.4	5.0	30
4.7										4*5.4	3.2	60	4*5.4	3.2	60	5*5.4	3.0	50
10							4*5.4	3.2	60	4*5.4	3.2	60	4*5.4	3.2	60	6.3*5.4	2.0	70
22	4*5.4	3.2	60	4*5.4	3.2	60	5*5.4	1.5	110	5*5.4	1.5	110	5*5.4	1.5	110	6.3*5.4	2.0	70
33	5*5.4	1.5	110	5*5.4	1.5	110	5*5.4	1.5	110	6.3*5.4	0.85	170	6.3*5.4	0.85	170	6.3*7.7	1.0	120
47	5*5.4	1.5	110	5*5.4	1.5	110	5*5.4	1.5	110	6.3*5.4	0.85	170	6.3*5.4	0.85	170	6.3*7.7	1.0	120
100	5*5.4	1.5	110	6.3*5.4	0.85	170	6.3*5.4	0.85	170	6.3*7.7	0.60	230	6.3*7.7	0.60	230	8*10.2	0.60	300
150	6.3*5.4	0.85	170	6.3*5.4	0.85	170	6.3*7.7	0.60	230	8*10.2	0.43	450	8*10.2	0.43	450	10*10.2	0.30	500
220	6.3*5.4	0.85	170	6.3*7.7	0.60	230	6.3*7.7	0.60	230	8*10.2	0.43	450	10*10.2	0.23	670	10*10.2	0.30	500
330	6.3*7.7	0.60	230	8*10.2	0.43	450	8*10.2	0.43	450	8*10.2	0.43	450	10*10.2	0.23	670			
470	8*10.2	0.43	450	8*10.2	0.43	450	8*10.2	0.43	450	10*10.2	0.23	670						
680	8*10.2	0.43	450	10*10.2	0.23	670	10*10.2	0.23	670									
1000	8*10.2	0.43	450	10*10.2	0.23	670												
1500	10*10.2	0.23	670															

額定紋波電流 Rated ripple current: (mA, 105°C, 100KHz); 阻抗值 Impedance: (Ω, 20°C, 100KHz)

■ 額定紋波電流的頻率系數 Frequency coefficient of rated ripple current


Frequency	50Hz	120Hz	300Hz	1KHz	≥10KHz
系數 Coefficient	0.64	0.80	0.85	0.93	1.00

注：以上所提供的設計及特性參數僅供參考，任何修改不做預先通知，如在使用上有疑問，請在採購前與我們聯絡，以便提供技術上的協助。
Note: all designs and specifications are for reference only and are subject to change without prior notice, if any doubt about safety for your application, please contact us immediately for technical assistance before purchase.

貼片鋁電解電容器編帶形狀及尺寸要求
Taping of Chip Type Aluminum Electrolytic Capacitor And Size


編帶 Carrier Tape

ΦD×L	4.0×5.4	5.0×5.4	6.3×5.4	6.3×7.7	8.0×6.5	8.0×10.2	10.0×10.2	8.0×12.0	10.0×12.0
W	12.0	12.0	16.0	16.0	16.0	24.0	24.0	24.0	24.0
P	8.0	12.0	12.0	12.0	12.0	16.0	16.0	16.0	16.0
F	5.5	5.5	7.5	7.5	7.5	11.5	11.5	11.5	11.5
A	4.7	6.0	7.0	7.0	8.7	8.7	10.7	8.7	10.7
B	4.7	6.0	7.0	7.0	8.7	8.7	10.7	8.7	10.7
T ₂	5.8	5.8	5.8	8.3	7.0	11.0	11.0	12.8	12.8




編帶包裝卷盤 Reel

ΦD×L	卷裝數量 Quantity/Reel	盒裝數量 Quantity/Bag	A
4.0×5.4	2000 pcs	20000 pcs	12.5
5.0×5.4	1000 pcs	10000 pcs	12.5
6.3×5.4	1000 pcs	10000 pcs	16.5
6.3×7.7	1000 pcs	10000 pcs	16.5
8.0×6.5	1000 pcs	10000 pcs	16.5
8.0×10.2	500 pcs	5000 pcs	24.5
10.0×10.2	500 pcs	5000 pcs	24.5
8.0×12.0	400 pcs	4000 pcs	24.5
10.0×12.0	400 pcs	4000 pcs	24.5




焊接方法和再流焊允許範圍 Soldering method and allowable range of the reflow

尺寸 Size	Thickness (mm)	TP(°C)	t1	t2	t3	Reflow cycles
Φ4.0~Φ6.3	≥2.5	260±0	120s	90s	5s	1
Φ8.0~6.5/12.0	≥2.5	240±0	100s	60s	5s	1
Φ10.0~10.2/12.0	≥2.5	235±0	100s	40s	5s	1



- 溫度上升平均每秒每分鐘最多3℃
Average ramp-up rate is 3℃/second max.
- 溫度下降平均每分鐘最多6℃
Ramp-down rate is 6℃/second max.
- 從25℃上升到峰值溫度時間最長不能超過7分鐘
Time from 25℃ to peak temperature is 7 minutes max.

表面安裝推薦尺寸 Recommended land size



尺寸Size	X	Y	a
Φ4.0	1.6	2.6	1.0
Φ5.0	1.6	3.0	1.4
Φ6.3	1.6	3.5	2.1
Φ8.0	2.5	3.5	3.0
Φ10.0	2.5	4.0	4.0

- 預熱進行的條件:不超過+150℃和120秒
Pre-heating shall be done less than +150℃ and for 120 seconds.
- 電容器頂部的溫度不超過+260℃
The temperature at capacitor top shall not exceed +260℃
- 電容器頂部的溫度在+200℃以上時，持續時間不超過90秒
The duration for over +200℃ at capacitor top shall not exceed 90 seconds
- 不同的再流焊方法，其溫度曲線不同。
The standard temperature profile differs by every reflow method.
- 如果電容器承受的條件與現流焊的允許範圍不同，請與我們聯系。
If the conditions capacitors can bear are different, from the allowable range of reflow.

注：以上所提供的設計及特性參數僅供參考，任何修改不做預先通知，如在使用上有疑問，請在採購前與我們聯絡，以便提供技術上的協助。
Note: all designs and specifications are for reference only and are subject to change without prior notice, if any doubt about safety for your application, please contact us immediately for technical assistance before purchase.