






- HOUSING HAS RAST 5 COMPLIANT KEYING LATCHING, AND POLARIZATION, TAB IS 6.30 x 0.8mm ACCORDING TO DIN 46224;
 - MATERIAL: HOUSING NYLON, UL94 V0, 750 °C GWT NO FLAME;
 - FINISH: CONTACTS, TIN PLATING OVERALL, NICKEL UNDER-PLATING;
 - PACKING: LOOSE PIECE OR TUBE. THE PART NUMBER IN THIS DRAWING ARE WITH LOOSE PIECE PACKING. PLEASE CONTACT TE SALES REPRESENTATIVES FOR TUBE PACKING REQUIREMENT.
- 5 PRELIMINARY, NOT FOR PRODUCTION.
- 6 MATERIAL: HOUSING PA66, UL94 V0
PRODUCT COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30 (GWT).
- 7 FINISH: CONTACT, SILVER PLATING OVERALL, NICKEL UNDER-PLATING.
- 8 SPECIAL VERSION: SHORT PEG DESIGN, DETAIL IN SHEET 3



42.30	40.30	8
37.30	35.30	7
32.30	30.30	6
27.30	25.30	5
22.30	20.30	4
17.30	15.30	3
12.30	10.30	2
N	M	NO.OF POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.P. APR162013	TE Connectivity	
CHK F.M. APR162013		NAME RAST 5 TAB HEADER ASSY DIN STYLE, TH, VERTICAL		
APVD - APR162013		PRODUCT SPEC 108-106080	SIZE CAGE CODE DRAWING NO A200779C=2232511	
APPLICATION SPEC -		WEIGHT -	RESTRICTED TO	
MATERIAL -		CUSTOMER DRAWING		
DIMENSIONS: mm		SCALE 4:1 SHEET 1 OF 3 REV A16		
TOLERANCES UNLESS OTHERWISE SPECIFIED:				
0 PLC ±0.5				
1 PLC ±0.25				
2 PLC ±0.13				
3 PLC ±0.0001				
4 PLC ±0.0001				
ANGLES FINISH				

4

3


2

1


THIS DRAWING IS UNPUBLISHED.
 RELEASED FOR PUBLICATION
 20

© COPYRIGHT 20 BY - ALL RIGHT REVERSED
 ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS			
P	LYR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-





3-2232511-3 $\Delta_5 \Delta_7$




2232511-5
 1-2232511-5 Δ_6
 2328608-5 Δ_8




2-2232511-3 Δ_5
 2232511-3
 1-2232511-3 Δ_6
 2328608-3 Δ_8




2232511-4




1-2232511-4



2-2232511-5 Δ_5



2232511-6



2232511-8

3 POS.


4 POS.

4 POS.




5 POS.

6 POS.




8 POS.




VOID PIN




PCB LAYOUT SKETCH
 SOLDER SIDE




2232511-7
 1-2232511-7 Δ_6
 2328608-7 Δ_8



2-2232511-7 Δ_6



3-2232511-7



PCB LAYOUT SKETCH
 SOLDER SIDE

7 POS.

NATURE

COLOR NO. OF POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN B.P. APR162013

CHK - 24SEP2013

APVD - 24SEP2013

PRODUCT SPEC


APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

SCALE 4:1 SHEET 2 OF 3 REV A16

8	2232511-8
7	3-2232511-7
7	2-2232511-7 Δ_6
7	1-2232511-7 Δ_6
7	2232511-7
6	2232511-6
5	2-2232511-5 Δ_5
5	1-2232511-5 Δ_6
5	2232511-5
4	1-2232511-4 Δ_5
4	2232511-4 Δ_5
3	3-2232511-3 $\Delta_5 \Delta_7$
3	2-2232511-3 Δ_5
3	1-2232511-3 Δ_6
3	2232511-3




TE Connectivity

RAST 5 TAB HEADER ASSY
 DIN STYLE, TH, VERTICAL



SIZE CAGE CODE DRAWING NO
 A200779C=2232511

RESTRICTED TO



LOC		DIST		REVISIONS			
P	LYR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	

△ SPECIAL VERSION: SHORT PEG DESIGN



OTHER DIMENSIONS SEE SHEET 1
KEYING SEE SHEET 2

NATURE	7	2328608-7
	5	2328608-5
	3	2328608-3
COLOR	NO. OF POS.	△ PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.P.	APRT62013	TE Connectivity	
DIMENSIONS: mm		CHK F.M.	APRT62013		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	APRT62013	NAME RAST 5 TAB HEADER ASSY DIN STYLE, TH, VERTICAL	
0 PLC ±.5		PRODUCT SPEC		SIZE	
1 PLC ±0.5		108-106080		CAGE CODE	
2 PLC ±0.25		APPLICATION SPEC		DRAWING NO	
3 PLC ±0.013		-		A200779C=2232511	
4 PLC ±0.0001		WEIGHT		RESTRICTED TO	
ANGLES ±.5		-		SCALE 4:1	
FINISH		CUSTOMER DRAWING		SHEET 3 OF 3	
-		-		REV A16	