

5414409-1

✓ ACTIVE

TE Internal #: 5414409-1

BNC RF Interface, Jack, 75 ohm, Bayonet, 4 GHz Operating Frequency, Cable-to-Board, 1 Position, Printed Circuit Board, Panel Mount

[View on TE.com >](#)[Connectors > RF Connectors > Coax Connectors > BNC RF Connector: 75 Ohm](#)RF Interface: **BNC**RF Connector Style: **Jack**RF Connector Mated Outer Diameter (Approximate): **14.53 mm [.572 in]**Impedance: **75 Ω**RF Connector Coupling Mechanism: **Bayonet**[All BNC RF Connector: 75 Ohm \(2\)](#)

Features

Product Type Features

RF Interface	BNC
RF Connector Style	Jack
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Right Angle
Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	75 Ω
-----------	------

Body Features

Body Material	Zinc
Body Plating Material	Nickel

Contact Features

RF Connector Center Contact Underplating Material	Nickel
	30 μ in

RF Connector Center Contact Plating Material	Gold
--	------

RF Connector Center Contact Material	Phosphor Bronze
--------------------------------------	-----------------

Termination Features

Termination Post & Tail Length	4.11 mm [.162 in]
--------------------------------	-------------------

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

PCB Mount Retention	With
---------------------	------

Panel Mount Feature Type	Lockwasher and Nut
--------------------------	--------------------

Panel Attachment Style	Rear Mount
------------------------	------------

RF Connector Coupling Mechanism	Bayonet
---------------------------------	---------

Connector Mounting Type	Panel Mount
-------------------------	-------------

RF Contact Captivation Method	Mechanical
-------------------------------	------------

Detent	With
--------	------

Dimensions

Mounting Post Length	3.48 mm [.137 in]
----------------------	-------------------

Profile Height from PCB	15.88 mm [.625 in]
-------------------------	--------------------

RF Connector Mated Outer Diameter (Approximate)	14.53 mm [.572 in]
---	--------------------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operating Temperature Range	-55 – 85 °C [-67 – 185 °F]
-----------------------------	----------------------------

Operation/Application

Operating Frequency	4 GHz
---------------------	-------

Packaging Features

Packaging Method	Tube
------------------	------

Other

Grade	Economy
-------	---------

Dielectric Material	Polymethylpentene
---------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com >

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Compliant with Exemptions
-----------------------------	---------------------------

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024 (241)

Candidate List Declared Against: JUNE 2024 (241)

SVHC > Threshold:

Pb (3.7% in Component Part)

Article Safe Usage Statements:

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1337481-0
SMB R/A PCB Skt 50Ohm Gold Plt



TE Part # 1-1337414-0
N Str Jk Hex 50Ohm Silver Pltd PSF 1/4M



TE Part # 1-1337420-0
BNC Str Plg MC 50Ohm Nickel Pltd RG58C/U



TE Part # 1-1478075-0
BNC R/A Plg Hex 50Ohm Silver Pltd RG58C/



TE Part # 1-1337630-0
N Str Plg Hex 50Ohm Nickel Plt




TE Part # 1-1337416-0
N Str Plg Hex 50Ohm Silver Pltd RG58C/U




TE Part # 1-1337629-0
N Str Plg Hex 50Ohm Nickel Pltd PSF 1/4M



TE Part # 1-1337412-0
N R/A Plg Hex 50Ohm Silver Pltd PSF 1/4M



Customers Also Bought



Documents

Product Drawings

BNC PCB RT ANG JACK W/POST

English

CAD Files

3D PDF

English

Customer View Model

[ENG_CVM_5414409-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_5414409-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_5414409-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BNC Connectors

English

Product Specifications

Product Specification

English