



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector EMC Shielding



Connector Shielding Accessory Type: **Shield**
Primary Product Material: **Copper Alloy**

Features

Product Type Features

Sealable	Yes
Connector Shielding Accessory Type	Shield

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Primary Product Material	Copper Alloy
--------------------------	--------------

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241)



Does not contain REACH SVHC




Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not reviewed for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # HDT-48-00 CRIMP TOOL, HAND	 TE Part # 9-2367337-3 2POS,CSS SIZE 20,SOC OUTER HSG ASSY,SLD	 TE Part # 9-2370624-1 CU ALLOY,OUTER FERRULE,DATA DT	 TE Part # 9-2370710-1 CU ALLOY,SHIELD ASSY,CONN HSG, DATA DT
 TE Part # 0462-201-2031 SOC, SOLID, SIZE 20, 20AWG, AU	 TE Part # 2386215-1 HDR SUB ASSY,2POS,PIN DIA 1.0,90 DEG	 TE Part # 9-2367337-1 2POS,CSS SIZE 20,SOC OUTER HSG ASSY,SLD	 TE Part # 9-2367337-2 2POS,CSS SIZE 20,SOC OUTER HSG ASSY,SLD
 TE Part # 9-2367337-4 2POS,CSS SIZE 20,SOC OUTER HSG ASSY,SLD	 TE Part # 9-2370624-2 CU ALLOY,OUTER FERRULE,DATA DT	 TE Part # 9-2370706-1 CU ALLOY,SHIELD ASSY,HDR,DATA DT	



Also in the Series

DEUTSCH DT Highspeed

Automotive Connector EMC Shielding (5)	Automotive Housings(2)	Connector Backshells(2)	Connector Seals & Cavity Plugs(2)
Data Connectivity Housings(1)	Infotainment & Multimedia Cable Assemblies(15)	Other Automotive Connector Accessories(6)	PCB Headers & Receptacles(3)

Customers Also Bought

TE Part #HDP24-18-14PE DEUTSCH HDP20 Housings	TE Part #9-2367346-1 SWS,HSD,CVTY DIA,RECTANGULAR	TE Part #9-2370624-1 CU ALLOY,OUTER FERRULE,DATA DT	TE Part #2386215-1 HDR SUB ASSY,2POS,PIN DIA 1.0,90 DEG
TE Part #9-2367337-1 2POS,CSS SIZE 20,SOC OUTER HSG ASSY,SLD	TE Part #9-2367341-1 2POS,CSS SIZE 20,PIN OUTER HSG ASSY	TE Part #9-2367344-3 PIN CONN CVR,2POS,CSS SIZE 20,180 DEG	TE Part #9-2367346-2 SWS,HSD,CVTY DIA,RECTANGULAR
TE Part #9-2370624-2 CU ALLOY,OUTER FERRULE,DATA DT			



Documents

Product Drawings
CU ALLOY,SHIELD ASSY,CONN HSG,DATA DT
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_9-2370714-1_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_9-2370714-1_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_9-2370714-1_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Application Specification
English