




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spade Tongue Terminal**
Wire Size: **509 – 3260 CMA**
Stud Size: **#2, M2**

Features

Product Type Features

Stud Size	#2, M2
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Contact Features

Spade Terminal Type	Spade Tongue Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	2.36 mm[.093 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	12.8 mm[.504 in]
Barrel Inside Diameter	1.55 mm[.061 in]



Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Method	Loose Piece
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 58545-1
SOLISTRAND 10-22 DIE ASSY

TE Part # 49935
DAHT SOLIS 22-10 ASSY

TE Part # 58546-1
PC 22-10 SOLISSPICE SPL I SHT

TE Part # 58545-3
SDE DIE ASSY. 22-10 SOLISTRAND

TE Part # 47812
DIES SOLIS 22-16 DIE SET

TE Part # 169400
CERTI-LOK FRAME W/O DIES

Customers Also Bought

TE Part #9556822004
DWTC-4/1-X-STK

TE Part #281839-4
HOUSING HE13 HE14 COSI 2X4 P

TE Part #1625971-7
HSA25 120R 5%

TE Part #3-1625999-2
HSC100 3R0 5%

TE Part #322799
SOLIS R HR 22-16COM22-18MIL 10

TE Part #5520470-3
MJ,R/A,6P/6C,TRAY PACK

TE Part #2-34151-1
PG R 22-16 COMM 22-18 MIL 5/16

TE Part #1658525-6
622-1053LF, PCB IDC, LEAD FREE

TE Part #1218124-2
15 POS,ASSY,PLUG,LOW PROF,109

TE Part #1-1337434-0
BNC RM BHJ Hex 50Ohm Silver Pltd
RG58C/U



Documents

Product Drawings

SOLIS SPD 22-16COMM 22-18MIL 2

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_53555-1_E_c-53555-1-e.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_53555-1_E_c-53555-1-e.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_53555-1_E_c-53555-1-e.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English