



SPLICE

TE Internal #: 61299-2
Pigtail Splice / Thru Splice, Serrated, 7000 – 12000 CMA Wire Size,
Brass, 3 Serration, Length 6.8 mm [.267 in], Reel, Open, SPLICE,
Splices

[View on TE.com >](#)

Terminals & Splices > Splices



Splice Type: **Pigtail Splice, Thru Splice**
Sealable: **No**
Splice Features: **Serrated**
Wire Size: **7000 – 12000 CMA**
Contact Base Material: **Brass**

Features

Product Type Features

Splice Type	Pigtail Splice, Thru Splice
Sealable	No
Compatible With Discrete Wire Type	Solid, Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Serrations	3
Compatible With Wire & Cable Type	Discrete Wire

Body Features

Product Weight	.629 g
Splice Features	Serrated

Contact Features

Contact Base Material	Brass
Barrel Type	Open



Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	7000 – 12000 CMA
Terminal Material Thickness	.78 mm[.031 in]
Product Length	6.8 mm[.267 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Packaging Quantity	3500
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 61300-1
[SPLICE IS 10000-16000 .031 TPST](#)



TE Part # 63414-1
[SPLICE 9000-16000 .031 TPST](#)



TE Part # 2837449-1
[OCEAN_2.0_Applicator-S-180F-RSM](#)



TE Part # 2837449-2
[OCEAN_2.0_Applicator-S-180F-RSA](#)



KIT
TE Part # 7-2837449-7
[OCEAN_2.0_SPARE_PART_KIT-180F](#)



TE Part # 566347-1
[STD STSAPR180F F](#)

Also in the Series | SPLICE





[Crimp Wire Pins, Tabs & Ferrules\(1\)](#)



[Splices\(64\)](#)

Customers Also Bought



 TE Part #485043-2 SPLICE 4000-9000 .020 TPBR	 TE Part #63625-2 SPLICE 5000 -16000 .025 TPBR	 TE Part #160859-4 FF 250 TAB 20-17 AWG .016 TPPB	 TE Part #63562-1 SPLICE 10400-22900 030TPBR
 TE Part #60372-1 SPLICE 1200-2600 .020 BR	 TE Part #63130-3 SPLICE REC. 1500-5000 .020 TPBR	 TE Part #62754-1 SPLICE 14000-30000 .030 BR	 TE Part #1394026-1 FLA-STE-GEH9,5MM 2P
 TE Part #890060-000 S1017-1.0X50	 TE Part #42142-2 SHUR PLUG TERMINAL 18-14 AWG BR		

Documents

Product Drawings

SPLICE 7000-12500 .032 TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_61299-2_AF_c-61299-2-af.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_61299-2_AF_c-61299-2-af.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_61299-2_AF_c-61299-2-af.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English

Agency Approvals

CSA Certificate

English