



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Cable Entry Location: **Bottom**

Hood & Base Locking Device Type: **Screwlock**

Sealable: **Yes**

Features

Product Type Features

Hood & Base Connector Product Type	Base Housing
Sealable	Yes

Body Features

Cable Entry Location	Bottom
----------------------	--------

Mechanical Attachment

Locking Device Location	Housing
Hood & Base Locking Device Type	Screwlock

Housing Features

Housing Material	Die Cast Aluminum
------------------	-------------------

Usage Conditions

Corrosion Protected	Yes
---------------------	-----

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

--	--



Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T1910240129-000
H24BPR-TSH-PG29



TE Part # T2040242201-000
HE-024-F



TE Part # T1910240132-000
H24BPR-TSH-M32



TE Part # T1910240140-000
H24BPR-TSH-M40




 TE Part # T1920240129-000 H24BPR-TGH-PG29	 TE Part # T1920240132-000 H24BPR-TGH-M32	 TE Part # T1920240140-000 H24BPR-TGH-M40	 TE Part # T1920240163-001 H24BPR-TGXH-XL-M63
 TE Part # T1920240321-000 H24BPR-TGH-3PG21	 TE Part # T1920240325-000 H24BPR-TGH-3M25	 TE Part # T1900242250-002 H24BPR-TG/SH-XL-2M50	 TE Part # T1910240121-000 H24BPR-TSH-PG21
 TE Part # T1910240125-000 H24BPR-TSH-M25	 TE Part # T1910240129-002 H24BPR-TSH-XL-PG29	 TE Part # T1910240132-002 H24BPR-TSH-XL-M32	 TE Part # T1910240136-000 H24BPR-TSH-PG36
 TE Part # T1910240136-002 H24BPR-TSH-XL-PG36	 TE Part # T1910240140-002 H24BPR-TSH-XL-M40	 TE Part # T1910240142-002 H24BPR-TSH-XL-PG42	 TE Part # T1910240148-002 H24BPR-TSH-XL-PG48

Also in the Series

HDC IP68 EMC

 Connector Caps & Covers(4)	 Rectangular Connector Hoods & Bases (444)
---	---

Customers Also Bought



Documents

Product Drawings

H24BPR-AG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_T1930240000-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_T1930240000-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_T1930240000-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Heavy Duty Connectors - HCM/IP68 Hoods/Housing Series

English



[Product Specifications](#)

[Application Specification](#)

English

[Application Specification](#)