



All Small Signal Relay, Axicom P2 Standard (30)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 2-1393789-5
V23079J1101B301

TE Part # 6-1393788-2
V23079D1011B301

Also in the Series | Axicom P2 Signal Relay

Signal Relays(56)

Customers Also Bought

TE Part #6609006-9
6EEJ1=F8013 S0

TE Part #2176070-7
3521 18R 1% 2W

TE Part #350430-4
04P UMNL PIN HDR ASSY NATL LF

TE Part #5555153-1
MJ,LPF,R/A,8P,PCBG,PSTP.15TTR

TE Part #1954289-2
Connector,Blade & Recpt 4 Pos

TE Part #8-1879665-8
H8 100K 0.1% 15PPM

TE Part #2160753002
55A0111-24-5

TE Part #309031-004
TU-40-050-28B



Documents

Product Drawings

V23079F1101B301

English

CAD Files

Customer View Model

ENG_CVM_1393788-4_A5.2d_dxf.zip

English

Customer View Model

ENG_CVM_1393788-4_A5.3d_igs.zip

English

Customer View Model

ENG_CVM_1393788-4_A5.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-1393788-3_F1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_7-1393788-3_F1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_7-1393788-3_F1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Axicom Signal and High Frequency Relays (RF Switches) APPLICATION NOTE #2

English

Transportation, Storage, Handling, Assembly and Testing of AXICOM SMT Relays

English

AXICOM Latching Relays

English

P2 Relay Datasheet



English

[Product Specifications](#)
[Definitions](#) [General Purpose Relays](#)

English

[Agency Approvals](#)
[UL](#)

English