



Terminals & Splices > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal Type: **Receptacle**

Mating Tab Width: **6.3 mm [.25 in]**

Mating Tab Thickness: **.8 mm [.031 in]**

Terminal Transmits: **25 – 40 A (Power)**

Wire Size: **20 – 15 AWG**

[All TIMER, RECEPTACLE AND TAB \(324\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	6.3mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	25 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	6.3 mm[.25 in]
Mating Tab Thickness	.8 mm[.031 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire



Dimensions

Compatible Insulation Diameter Range	2 – 3 mm[.079 – .118 in]
Wire Size	.5 – 1.5 mm ²
Wire Size Search	15 AWG, 16 AWG, 17 AWG, 18 AWG, 19 AWG, 20 AWG
Tab Length	19 mm[.75 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	110 °C[230 °F]
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Compatible With Agency/Standards Products	IEC 664/664A (DIN VDE 0110)
---	-----------------------------

Packaging Features

Packaging Quantity	2500
Packaging Method	Reel

Other

Terminal Transmits	25 – 40 A (Power)
--------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1579007-4 EXTRACTION TOOL	 TE Part # 4-1579007-3 EXTRACTION TOOL KIT	 TE Part # 2063375-1 SDE JPT 0.5-2.5mm2 ASSY	 TE Part # 2063375-2 SDE JPT 0.5-2.5mm2 DIE SET
 TE Part # 2151261-1 OCEAN_2.0_Applicator-S-090F140F-RSM	 TE Part # 2151261-2 OCEAN_2.0_Applicator-S-090F140F-RSA	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 7-2151261-7 OCEAN_2.0_SPARE_PART_KIT-090F140F

Also in the Series | Standard Timer

 Automotive Housings(2)	 Automotive Terminals(11)	 Connector Contacts(2)	 Plug & Socket Lighting Connectors(2)
---	---	--	---



Standard Edge Connectors(11)



Wire-to-Board Connector Assemblies
& Housings(11)

Customers Also Bought



TE Part #953697-2
MQS, CONNECTOR HOUSING



TE Part #1-2176057-5
RLP73M 3A R039 1% 1K RL



TE Part #3-928343-8
STD-TIMER GEH 8P



TE Part #63442-1
PL 250 TERMINAL REC 18-14 AWG
TPBR



TE Part #1-100605-2
250 FASTON,REC.,14-17AWG,PTPB



TE Part #1803018-3
CRIMPER, INSUL O



TE Part #2-1803224-4
CRIMPER,WIRE F



TE Part #2217984-3
ANVIL



TE Part #CD41583001
55E0211-0.50-0(B01)

Documents

Product Drawings

STC REC 6.3 Contact SRC Sn

English

CAD Files

Customer View Model

ENG_CVM_CVM_926965-1_G.2d_dxf.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_926965-1_G.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_926965-1_G.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Application Specification

English