


PLASTI-GRIP

TE Internal #: 8-52947-1
Spring Spade Terminal, 22 – 16 AWG, #4 / M2.5 Stud Size, 2.84 mm
[.112 in] Stud Diameter, Closed Barrel, Straight, Tin, PLASTI-GRIP
[View on TE.com >](#)



Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spring Spade Terminal**
Wire Size: **509 – 3260 CMA**
Stud Size: **#4, M2.5**

Features

Product Type Features

Stud Size	#4, M2.5
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Body Features

Insulation Sleeve Color	Red
Stripe Color	Red

Contact Features

Spade Terminal Type	Spring Spade Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	2.84 mm[.112 in]
Tongue Thickness	.84 mm[.033 in]
Product Length	20.6 mm[.811 in]
Compatible Insulation Diameter (Max)	3.56 mm[.14 in]
Compatible Insulation Diameter Range	2.67 – 3.56 mm[.105 – .14 in]

Usage Conditions

Insulation Option	Partially Insulated
Operating Temperature Range	90 °C[194 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58433-3 PRO CR ASSY, RBY IS9252	TE Part # 58423-1 DIE, RBY IS9252	TE Part # 47386 DAHT PG PIDG 26-16 ASSY	TE Part # 169404 CERTI-LOK DIE

Also in the Series | PLASTI-GRIP

Compression Connectors(3)	Crimp Wire Pins, Tabs & Ferrules(19)	Ring Terminals(300)	Spade Terminals(160)

Splices(46)

Customers Also Bought





TE Part #206966-9
CPC Cable Clamps



TE Part #3-640441-2
02P MTA100 CONN ASSY WHT



TE Part #66104-8
III+ SKT,24-20,15AU/FL,STRIP



TE Part #4-1393127-9
PRD-11DH0-24=PRD



TE Part #87224-4
04 MODII HDR SRST UNSHRD .100



TE Part #87224-6
06 MODII HDR SRST UNSHRD .100



TE Part #66102-3
III+ PIN,24-20,15AU/FL,STRIP



TE Part #2-1393250-3
W28-XQ1A-1=W28-



TE Part #ADP-SMAM-SMAM-G
SMA Plug to SMA Plug

Documents

Product Drawings
PG SP SPD 22-16COMM 22-18MIL 4
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_8-52947-1_G.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_8-52947-1_G.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_8-52947-1_G.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English

Instruction Sheets

AMP* PIDG* (VINYL) & PLASTI-GRIP* SHORT SPRING SPADE TERMINALS FOR BAR

English

Instruction Sheet (U.S.)

English