

CA-06S1N1280DNS - Cable connector



1619605

<https://www.phoenixcontact.com/us/products/1619605>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, straight, shielded: yes, SPEEDCON, No. of pos.: 6, Direction of rotation: Standard, contact connection type: Socket, Solder connection, cable diameter range: 3 mm ... 14.5 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1243696

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Reduced connection time with SPEEDCON fast locking system
- Solder connection: proven connection technology for various litz wires

Commercial data

| | |
|--------------------------------------|--------------------|
| Item number | 1619605 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB31 |
| Product key | ABRAEB |
| Catalog page | Page 84 (C-2-2019) |
| GTIN | 4046356822695 |
| Weight per piece (including packing) | 97 g |
| Weight per piece (excluding packing) | 93 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

CA-06S1N1280DNS - Cable connector



1619605

<https://www.phoenixcontact.com/us/products/1619605>

Technical data

Product properties

| | |
|------------------------|---------------------------------|
| Product type | Circular connector (cable-side) |
| Data management status | |
| Article revision | 08 |

Connector

Connection 1

| | |
|-------------|--------|
| Head design | Socket |
|-------------|--------|

Insulating body

| | |
|------------------------------------|---------------------|
| Coding | N |
| Insulation body material | PBT |
| Contact material | CuZn |
| Contact surface material | Ni/Au |
| Insertion/withdrawal cycles | 100 |
| Connection method | Solder connection |
| Contact switching type | Socket |
| Application | Signal |
| Number of positions | 6 |
| Direction of rotation | Standard |
| Connection profile | 6 |
| Rated voltage | 48 V AC |
| | 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Contact diameter | 2 mm |
| Litz wire cross-section | 2.5 mm ² |
| Nominal current per signal contact | 20 A |

Signal contacts

Signal contacts max.

Housing

| | |
|-----------------------------------|-------------|
| Housing material | CuZn, GD-Zn |
| Type of locking | SPEEDCON |
| Pg screw connection | none |
| Degree of protection (plugged in) | IP67 |
| Thread type | M23 |

Seal

| | |
|-------------------------|------------------|
| External cable diameter | 3 mm ... 14.5 mm |
| Seal material | NBR |

CA-06S1N1280DNS - Cable connector



1619605

<https://www.phoenixcontact.com/us/products/1619605>

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
|---------------------------------|-------------------|

CA-06S1N1280DNS - Cable connector


1619605

<https://www.phoenixcontact.com/us/products/1619605>



Drawings

Schematic diagram



Connector pin assignment

CA-06S1N1280DNS - Cable connector





1619605

<https://www.phoenixcontact.com/us/products/1619605>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1619605>

| | | | | |
|------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|  cUL Recognized Approval ID: E335019-20141210 | | | | |
| | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| | 48 V | 10 A | 14 - 14 | - |

| | | | | |
|-----------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|--------------------------------|-------------------|-------------------------------|
|  UL Recognized Approval ID: E335019-20141210 | | | | |
| | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| | 48 V | 20 A | 14 - 14 | - |

| | | | | |
|-------------------------|--|--|--|--|
| cULus Recognized | | | | |
|-------------------------|--|--|--|--|

CA-06S1N1280DNS - Cable connector



1619605

<https://www.phoenixcontact.com/us/products/1619605>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27440102 |
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440116 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CA-06S1N1280DNS - Cable connector



1619605
<https://www.phoenixcontact.com/us/products/1619605>

Environmental product compliance

| | |
|-----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | dcbf5023-9f34-462e-ac76-7844f8c5b36d |

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com