




PLASTI-GRIP

TE Internal #: 53242-2
Spring Spade Terminal, 22 – 16 AWG, #10 Stud Size, 4.83 mm [.19 in] Stud Diameter, Closed Barrel, Straight, Tin, Partially Insulated, PLASTI-GRIP

[View on TE.com >](#)

Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spring Spade Terminal**
Wire Size: **509 – 3260 CMA**
Stud Size: **#10**

Features

Product Type Features

Stud Size	#10
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Electrical Characteristics

Voltage Rating	1000 V, 600 V
----------------	---------------

Body Features

Insulation Sleeve Color	Red
Stripe Color	Red
Product Weight	2.027 g

Contact Features

Spade Terminal Type	Spring Spade Terminal
Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment



Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	4.83 mm[.19 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	23.37 mm[.92 in]
Compatible Insulation Diameter (Max)	3.56 mm[.14 in]
Compatible Insulation Diameter Range	2.67 – 3.56 mm[.105 – .14 in]

Usage Conditions

Insulation Option	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	5000
Packaging Method	Tape & Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58433-3
PRO CR ASSY, RBY IS9252

TE Part # 58423-1
DIE, RBY IS9252

TE Part # 47386
DAHT PG PIDG 26-16 ASSY

TE Part # 47806-2
DIES PIDG 22-16 DIE SET

TE Part # 169404
CERTI-LOK DIE

TE Part # 1SET191001R0000
CRIMP-HT

Also in the Series | PLASTI-GRIP

Compression Connectors(3)

Crimp Wire Pins, Tabs & Ferrules(19)


Ring Terminals(300)

Spade Terminals(160)



Splices(46)

Customers Also Bought



TE Part #1-640550-2
12P MTA100 COVER



TE Part #1376394-1
5MM POWER KEY D/L PLATE GREEN



TE Part #61944-2
250 FASTON REC 18-14 AWG TPBR



TE Part #42110-3
RING TERMINAL 18-14 AWG BR



TE Part #7-2378159-2
Power Versa-Lock PLUG, 1X2 KEY G




TE Part #7-2232263-4
POWER TRIPLE LOCK: Glow Wire Cap



TE Part #520197P044
RT-3-NO.2-0-1.125IN



TE Part #2-31807-2
TERMINAL, SOLIS R 8 10



TE Part #1742539-3
CLUSTER BLOCK RECEPT, TPCuFeP

Documents

Product Drawings

PG SPR SPD 22-16COM22-18MIL 10

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_53242-2_J.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_53242-2_J.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_53242-2_J.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_53242-2_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_53242-2_K.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_53242-2_K.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL Report

English