


6450833-7

✓ ACTIVE

MULTI-BEAM | MULTI-BEAM XLE

TE Internal #: 6450833-7

Connector Assembly, Plug, Board-to-Board, 7 Position, 7.62 mm [.3 in] Centerline, Printed Circuit Board, MULTI-BEAM XLE, Rectangular Power Connectors

[View on TE.com >](#)[Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors](#)Rectangular Power Connector Type: **Connector Assembly**Connector & Housing Type: **Plug**Connector System: **Board-to-Board**Number of Positions: **7**Centerline (Pitch): **7.62 mm [.3 in]****Features****Product Type Features**

Assembly Requirement	Factory Assembled
Rectangular Power Connector Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Mating & Unmating Configuration	Normal
Number of Positions	7
PCB Mount Orientation	Right Angle
Number of Power Positions	7
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VDC
-------------------	---------

Body Features

Wire Color (Base)	Black
-------------------	-------

Contact Features

Contact Mating Area Plating Material	Gold
Contact Underplating Material	Nickel
Contact Current Rating (Max)	50 A
Contact Retention Within Housing	Without
Contact Type	Blade
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	.76 μm [30 μin]

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	7.62 mm [.3 in]
Housing Color	Black
Housing Material	High Temperature Thermoplastic

Usage Conditions

Operating Temperature Range	-40 – 125 °C [-40 – 257 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	High Temperature Part - Not Glow Wire

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | **MULTI-BEAM XLE**

Customers Also Bought

 <p>TE Part #1-1462037-4 IM03GR=IM RELAY 140mW 5V</p>	 <p>TE Part #1558666-3 T9GS1L14-12</p>	 <p>TE Part #4-1879378-1 TLR 2512 2.0W R0025 1% 150PPM 2K RL</p>	 <p>TE Part #5-1879233-3 SMW5 15R 5%</p>
--	--	---	---



Documents

Product Drawings

MBXLE R/A HDR 7ACP

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_6450833-7_C3.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6450833-7_C3.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6450833-7_C3.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English