


VIP-2/SC/FLK50 (1-40) /S7 - Passive module



2315243

<https://www.phoenixcontact.com/us/products/2315243>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE interface module for Siemens SIMATIC® S7-300, with SIMATIC®-specific labeling (1 - 40), with screw connection, module width: 106.1 mm

Commercial data

Item number	2315243
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	CK211S
Catalog page	Page 506 (C-5-2019)
GTIN	4046356313087
Weight per piece (including packing)	213.6 g
Weight per piece (excluding packing)	211 g
Customs tariff number	85366990
Country of origin	US

VIP-2/SC/FLK50 (1-40) /S7 - Passive module



2315243

<https://www.phoenixcontact.com/us/products/2315243>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	50
No. of channels	2
	4
	6
	8
	16
	24
	32

Data management status

Article revision	08
------------------	----

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Max. permissible operating voltage	25 V AC
	60 V DC
Max. current carrying capacity per branch	1 A
Rated surge voltage	0.6 kV

Supported controller ALLEN-BRADLEY PLC 5

Suitable I/O card	1771 OBN
-------------------	----------

Connection data

Field level

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M 3
Number of positions	42
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Controller level

Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	50

VIP-2/SC/FLK50 (1-40) /S7 - Passive module



2315243

<https://www.phoenixcontact.com/us/products/2315243>

Pitch	2.54 mm
-------	---------

Signaling

Status display	no
Status display present	No

Dimensions

Item dimensions	
Width	106.1 mm
Height	65.5 mm
Depth	56 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Housing insulation material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

VIP-2/SC/FLK50 (1-40) /S7 - Passive module




2315243

<https://www.phoenixcontact.com/us/products/2315243>

Drawings

Circuit diagram



VIP-2/SC/FLK50 (1-40) /S7 - Passive module



2315243

<https://www.phoenixcontact.com/us/products/2315243>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2315243>

	CSA Approval ID: 2122203			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	30 - 12	-

	cUL Recognized Approval ID: E238705			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	30 - 12	-

	UL Recognized Approval ID: E238705			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	30 - 12	-

	CSAus Approval ID: 2122203			
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	30 - 12	-

cULus Recognized

cCSAus

VIP-2/SC/FLK50 (1-40) /S7 - Passive module



2315243

<https://www.phoenixcontact.com/us/products/2315243>

Classifications

ECLASS

ECLASS-11.0	27141152
ECLASS-13.0	27141152
ECLASS-12.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2315243
<https://www.phoenixcontact.com/us/products/2315243>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com