




Connectors > Socket Connectors > Pin Sockets



Socket Length: 18.8 mm [.74 in]

Wire Size: .518 – 1.31 mm²

Connector System: Cable-to-Cable

Sealable: No

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Connector System	Cable-to-Cable
Sealable	No

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Dimensions

Socket Length	18.8 mm[.74 in]
Wire Size	.518 – 1.31 mm ²

Operation/Application

Solder Process Feature	None
Circuit Application	Power & Signal

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp



TE Part # 2836195-1
OCEAN-2.0-APPLICATOR-S-090F130F-RSM



TE Part # 2836195-2
OCEAN-2.0-APPLICATOR-S-090F130FA-RSA




TE Part # 7-2836195-7
OCEAN_2.0_SPARE_PART_KIT-090F130F


Customers Also Bought




TE Part #66103-2
III+ PIN,24-20,TIN-LEAD,LP




TE Part #1-350346-0
03P .140 MNL PLUG P/M NAT




TE Part #680106-000
D-609-05




TE Part #640417-2
BLADE REC 250 18-14AWG TPBR



TE Part #680104-000
D-609-03




TE Part #1-2176331-3
CRGP 2512 100R 1%




TE Part #156160-001
22759/32-22-1



TE Part #2-35109-1
PIDG 12-10 R 10; TAPE



TE Part #350200-1
.140 DIA SOK 14-10 PTPBR



TE Part #NB14644001
VERSAFIT-3X-1/4-0-SP

Documents

Product Drawings

MINI-SPRING RECEPTACLE 20-16 AWG PTPPHBZ

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_643222-2_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_643222-2_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_643222-2_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

EB**General Application Specification for Open Barrel Terminals

English

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

643222-2

Socket Length 18.8 mm [.74 in], .518 – 1.31 mm² Wire Size, 20 – 16 AWG Wire Size,
Cable-to-Cable, Power & Signal, Pin Sockets

