




Connectors > PCB Connectors > Backplane Connectors > Eurocard Connectors



Connector & Housing Type: **Plug**
Connector System: **Board-to-Board**
Termination Post & Tail Length: **3 mm [.118 in]**
Number of Positions: **48**
Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Connector & Housing Type	Plug
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board
DIN Size	Half
DIN Level	II

Configuration Features

Number of Positions	48
Number of Rows	3
PCB Mount Orientation	Right Angle
Number of Columns	16
Number of Signal Positions	48
Rows Loaded	A, C

Termination Features

Termination Post & Tail Length	3 mm[.118 in]
--------------------------------	---------------

Mechanical Attachment



Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
--------------------	----------------

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts






TE Part # 5650479-5
ASSY,PIN,EUROCARD,TYPE R/2,LEAD-FREE,48



TE Part # 5535070-5
ASSY,RECEPTACLE,EUROCARD,TYPE



TE Part # 5650916-5
ASSY,PIN,EUROCARD,TYPE C/2,LEA



TE Part # 5650478-5
ASSY,PIN,EUROCARD,TYPE C/2,LEA




TE Part # 5535034-5
ASSY,RECEPTACLE,EUROCARD,TYPE C/2,L-FREE



TE Part # 5148020-5
ASSY,PIN,EURO,"C/2",L-FREE,48



TE Part # 5536397-5
ASSY,RECEPT,EURO,TYPE C/2,LEAD



TE Part # 535034-5
048 EURO TYPE C RECEPT AP ASSY



TE Part # 5650948-5
ASSY,PIN,EUROCARD,TYPE C/2,LEA



TE Part # 926040-2
48P MOD 4 HSG




TE Part # 5535091-5
ASSEMBLY,RECEPTACLE,EUROCARD,T



TE Part # 5536484-5
ASSY,RECEPT,EURO,TYPE C/2,L-FR



TE Part # 4-1393637-4
V42254P2263C480=PC612 FEDERLEI



TE Part # 650478-5
048 EURO TYPE C PIN ST ASSY




TE Part # 1393640-7
V42254B2101C480=PC612 FEDERLEI



TE Part # 1393642-9
V42254B2240C480=PC612 FEDERLEI



TE Part # 926040-1
48P MOD 4 HSG



TE Part # 8-1393640-5
V42254B2201C480=PC612 FEDERLEI



TE Part # 2-1393641-5
V42254B2202C480=PC612 FEDERLEI

Customers Also Bought



TE Part #3-647502-4
04P MTA100 HDR ASSY,SM,SN, LF

TE Part #1623804-5
SQZ10 22R 5% WIRE

TE Part #3-641210-5
05P MTA156 HDR FLRA FB 30AU LF

TE Part #216446-1
6/6 PCB MOD.JACK BE

TE Part #5536397-5
ASSY,RECEPT,EURO,TYPE C/2,LEAD

TE Part #174467-1
070 MULTILOCK 10P ASSY SGL ROW

TE Part #1-1393224-8
RYA32024

TE Part #254887-E
STVC/2 48 F ABC VVW 7-00 EE 4,0 * 247 E0

TE Part #3-644767-6
06P MTA156 HDR ASSY FL ST LF

TE Part #2170463-1
MJ,INV,1X1,PNL G.,100"ST,SN

Documents

Product Drawings
48P.IEC-C MALE CONN

English

CAD Files
Customer View Model
ENG_CVM_CVM_216398-4_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model
ENG_CVM_CVM_216398-4_B.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_216398-4_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals



UL Report

English