




MTA 100

TE Internal #: 3-644312-3

Connector Assembly, Receptacle, Mating Alignment, Polarization
Mating Alignment Type, Mating Retention, MTA 100, Standard
Rectangular Connectors

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors > Nylon Tin Plated Receptacle: 2.54 mm, with Mating Alignment, MTA 100



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Mating Alignment: **With**
Mating Alignment Type: **Polarization**
Mating Retention: **With**

[All Nylon Tin Plated Receptacle: 2.54 mm, with Mating Alignment, MTA 100 \(127\)](#)

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Insertion Force Type	Normal
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Cavities	3
Contacts Preloaded	Yes
Number of Positions	3
Number of Rows	1



Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Type	Receptacle
Wire Contact Termination Area Plating Material	Tin
Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Tin
Contact Retention Within Housing	With
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Mating Alignment	With
Mating Alignment Type	Polarization
Mating Retention	With
Mating Retention Type	Locking Ramp
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Housing Color	Black
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Compatible Insulation Diameter (Max)	1.52 mm[.06 in]
Connector Height	13.21 mm[.52 in]
Product Width	6.99 mm[.275 in]
Product Length	7.62 mm[.3 in]
Wire Size	.2 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	No
----------	----





Circuit Application	Signal
Industry Standards	
CSA Rating	LR 7189
UL Rating	Recognized
Compatible With Agency/Standards Products	CSA, UL
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Quantity	500
Packaging Method	Package
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # CAT-104MTA-PRSMH PCB Header, Right Angle, Polyester, 2.54 mm	 TE Part # CAT-104MTA-PVUNH PCB Header: Polyester, Vertical, Unshrouded, No Mating Alignment	 TE Part # CAT-104MTA-NYLCC Nylon PCB Connector Covers: 2.54 mm, MTA 100	 TE Part # CAT-104MTA-PLSCC Polyester PCB Connector Covers: 2.54 mm, MTA 100
 TE Part # 640454-3 03P MTA100 HDR ASSY SQ STR POL	 TE Part # CAT-104MTA-NVSMH PCB Header: Nylon, Vertical, Surface Mount, MTA 100	 TE Part # CAT-104MTA-PRUSH PCB Header: Polyester, Right Angle, Unshrouded	 TE Part # CAT-104MTA-PVSHH Polyester Vertical PCB Header: 2.54 mm, Shrouded, MTA 100
 TE Part # CAT-104MTA-PVBRH Polyester Vertical PCB Header: 2.54 mm, Breakaway, MTA 100	 TE Part # CAT-104MTA-PRUMH PCB Header: Polyester, Right Angle, 2.54 mm	 TE Part # 3-647051-3 03P MTA100 HRD ASSYF/L HT LF	 TE Part # 58074-1 MTA 50/100/156 MANUAL TOOL FRAME
 TE Part # 58579-1 MTA 100 MANUAL TOOL ASSEMBLY DISCRETE	 TE Part # 3-647050-3 03P MTA100 HDR ASSY F/L HITEMP	 TE Part # 58246-3 MTA 100 CRIMP HEAD PRODUCTION RBBN CABLE	 TE Part # 58246-2 MTA 100 CRIMP HEAD PRODUCTION DISCRETE

Also in the Series | MTA 100

 Connector Caps & Covers(69)	 Connector Contacts(8)	 Connector Hardware(1)	 Insertion & Extraction Tools(2)
--	---	--	--



PCB Headers & Receptacles(441)



Standard Rectangular Connectors(495)



Wire-to-Board Connector Assemblies
& Housings(1)

Customers Also Bought



TE Part #3-640441-4
04P MTA100 CONN ASSY WHT



TE Part #3-643814-2
02P MTA100 CONN ASSY POL RIB



TE Part #640455-3
03P MTA100 HDR ASSY SQ R/A POL




TE Part #3-1393250-3
W28-XQ1A-20=W28



TE Part #794617-2
2POS,MICRO MNL,RCPT HSG



TE Part #794617-4
4POS,MICRO MNL,RCPT HSG




TE Part #1-104480-6
SHORT POINT RECP CONT LP



TE Part #YDTS20W11-05PAV001
RECP ASSY



TE Part #2-1393250-3
W28-XQ1A-1=W28-



TE Part #5-102699-4
10 MODII HDR DRST SHRD A/PIN

Documents

Product Drawings

03P MTA100 CONN ASSY BLK SPCL

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_3-644312-3_G.3d_igs.zip



English

Customer View Model

[ENG_CVM_3-644312-3_G.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_3-644312-3_G.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL](#)

English