




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spade Tongue Terminal**

Wire Size: **1624 – 4106 CMA**

Stud Size: **#10**

Features

Product Type Features

Shape Description	Square Spade
Stud Size	#10
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Contact Base Material	Brass
Spade Terminal Type	Spade Tongue Terminal
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Unplated
Contact Underplating Material	None

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.1 in
--	-------



Wire Size	1624 – 4106 CMA
Stud Diameter	4.82 mm[.19 in]
Tongue Thickness	.46 mm[.018 in]
Product Length	20.32 mm[.8 in]
Barrel Inside Diameter	1.65 mm, 3.04 mm[.065 in][.12 in]
Compatible Insulation Diameter (Max)	3.56 mm[.14 in]
Compatible Insulation Diameter Range	2.54 – 3.56 mm[.1 – .14 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	12000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as






EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 61498-1 SPADE 28-22 AWG .0157 X .310 BR	 KIT TE Part # 7-2150380-7 OCEAN_2.0_SPARE_PART_KIT-110F160F	 TE Part # 2150380-1 OCEAN_2.0_APPLICATOR-E-110F160F-REM	 TE Part # 2150380-2 OCEAN_2.0_APPLICATOR-E-110F160FA-REA
 TE Part # 2150575-1 OCEAN_2.0_APPLICATOR-E-110F160F-REM	 TE Part # 2150575-2 OCEAN_2.0_APPLICATOR-E-110F160F-REA	 KIT TE Part # 7-2150575-7 OCEAN_2.0_SPARE_PART_KIT-110F160F	

Customers Also Bought

 TE Part #1375820-2 CST-100 II HOUSING 2 POS	 TE Part #66507-9 PIN CONTACT, 20 DF	 TE Part #41202 250 FASTON,REC.,18-14 AWG,BR	 TE Part #42617-1 187 FASTON REC 20-16 AWG BR
 TE Part #62428-2 250 FASTON REC 12-10 AWG TPBR	 TE Part #1375819-1 CST-100 II CONTACT TIN PLT	 TE Part #60772-1 RING CRIMP 18-14 AWG BR	 TE Part #41343 SPADE 164(4.17MM) 20-16 AWG TPBR



TE Part #3-520106-2
ULTRA-FAST 250 ASY TAB 16-14 AWG
TPBR



TE Part #61359-1
RING GR ANTI ROTATIONAL 18-14
AWG PTPST

Documents

Product Drawings

SPADE TERMINAL 18-14 AWG BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60775-1_M_c-60775-1-m.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_60775-1_M_c-60775-1-m.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_60775-1_M_c-60775-1-m.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English