



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

[Catalog](#)

Number of contacts Low Voltage	1
Wire Size/AWG	26 - 18
Plug	Plug - Elbow
Locking system	Push-pull
Jacket cable outside diameter [mm]	4.30 - 5.20 mm
Suggested matching part	<a href="#">ERA.0S.116.CTL</a>
Series	S - Indoor Stepped Insert

[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/fla-0s-116-ctak52.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/fla-0s-116-ctak52.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

# Technical details

## Electrical Configuration

Contact Termination Low voltage	Solder
Insert configuration value	0S.116 - 1 Low Voltage
Insulator	T: PTFE
Rated current	12 A
Vtest (contact-contact)	1500 V (AC), 2100 V (DC)
Vtest (contact-shell)	1500 V (AC), 2100 V (DC)
Contact Type	Solder
Contact Dia.	1.6
Number of contacts Low Voltage	1
Wire Size/AWG	26 - 18

## Form & Material

Shell style / Model id	FLA - Elbow plug, cable collet
Plug	Elbow
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Colour	Gray
Weight	17.73 g

## Environment

Technical domain	Audio Video, Energy and Industrial, Semiconductor, Test and Measurement
Environmental sealing (IP rating)	IP50
Temperature range	-55°C / +250°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	75 dB (10 MHz)
Shielding (min)	40 dB (1 GHz)
Shock Resistance	100 g [ 6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>144 hr


[https://www.lemo.com/int\\_en/solutions/originals/s-indoor-stepped-insert/fla-0s-116-ctak52.html](https://www.lemo.com/int_en/solutions/originals/s-indoor-stepped-insert/fla-0s-116-ctak52.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	4.30 - 5.20 mm

Drawings



Dimensions

	A	H	L	M	S1	S2	A1
mm.	13	24.5	23	13	8	6.5	13
in.	0.51	0.96	0.91	0.51	0.31	0.26	0.51