


SOD-323
FEATURES

For use in low voltage, high frequency inverters
 Free wheeling, and polarity protection applications.


MARKING: SL





Maximum Ratings and Electrical Characteristics, Single Diode @Ta=25°C

Parameter	Symbol	B0540WS	Unit
Non-Repetitive Peak Reverse Voltage	V_{RM}	40	V
Peak Repetitive Peak Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V_{RRM} V_{RWM} V_R	40	V
RMS Reverse Voltage	$V_{R(RMS)}$	28	V
Average Rectified Output Current	I_O	1	A
Peak Forward Surge Current @t=8.3ms	I_{FSM}	25	A
Repetitive Peak Forward Current	I_{FRM}	1.5	A
Power Dissipation	P_d	200	mW
Thermal Resistance Junction to Ambient	$R_{\theta JA}$	625	°C/W
Storage Temperature	T_{STG}	-55~+150	°C

ELECTRICAL CHARACTERISTICS (Ta=25°C unless otherwise specified)

Parameter	Symbol	Test conditions	Min	Max	Unit
Reverse breakdown voltage	$V_{(BR)}$	$I_R = 1mA$	40		V
Reverse voltage leakage current	I_R	$V_R = 40V$		1	mA
Forward voltage	V_F	$I_F = 1A$ $I_F = 3A$		0.6 0.9	V
Diode capacitance	C_D	$V_R = 4V, f = 1MHz$		120	pF



Typical Characteristics



PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SOD-323



UNIT	A	b _p	C	D	E	H _E	A ₁	L _p
mm	1.20 0.90	0.40 0.25	0.15 0.10	1.80 1.60	1.35 1.15	2.80 2.30	0.10 0.01	0.50 0.20