

CA-09S1N1290DN - Coupler connector



1620164

<https://www.phoenixcontact.com/us/products/1620164>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Coupler connector, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Socket, Solder connection, cable diameter range: 3 mm ... 14.5 mm, coding: N, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1244053

Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

Commercial data

Item number	1620164
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB31
Product key	ABRAEG
Catalog page	Page 88 (C-2-2019)
GTIN	4046356818810
Weight per piece (including packing)	93.1 g
Weight per piece (excluding packing)	93.1 g
Customs tariff number	85366990
Country of origin	DE

CA-09S1N1290DN - Coupler connector



1620164

<https://www.phoenixcontact.com/us/products/1620164>

Technical data

Product properties

Product type	Circular connector (cable-side)
Data management status	
Article revision	04

Connector

Connection 1	
Head design	Socket

Insulating body	
Coding	N
Insulation body material	PBT
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Socket
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Contact diameter Power contacts	2 mm
Litz wire cross-section Power contacts max.	2.5 mm²
Rated current Power contacts	20 A
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Contact diameter Signal contacts	1 mm
Litz wire cross-section Signal contacts max.	1 mm²
Nominal current per signal contact	8 A

Housing	
Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

CA-09S1N1290DN - Coupler connector



1620164

<https://www.phoenixcontact.com/us/products/1620164>

Seal

External cable diameter	3 mm ... 14.5 mm
Seal material	NBR

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

CA-09S1N1290DN - Coupler connector

1620164

<https://www.phoenixcontact.com/us/products/1620164>



Drawings

Schematic diagram



Connector pin assignment

CA-09S1N1290DN - Coupler connector



1620164

<https://www.phoenixcontact.com/us/products/1620164>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1620164>

cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Power	48 V	12 A	14 - 14	-
Signal	48 V	6 A	18 - 18	-

UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Power	48 V	20 A	14 - 14	-
Signal	48 V	8 A	18 - 18	-

cULus Recognized				
------------------	--	--	--	--

CA-09S1N1290DN - Coupler connector



1620164

<https://www.phoenixcontact.com/us/products/1620164>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CA-09S1N1290DN - Coupler connector



1620164
<https://www.phoenixcontact.com/us/products/1620164>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	21978362-0494-4a19-a42e-4145d0344a35

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com