




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 8233 – 10382 CMA

Stud Size: #10

Features

Product Type Features

Terminal Features	Sheared
Shape Description	RING-001
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#10
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	1.205 g
----------------	---------

Contact Features

Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin

Mechanical Attachment

--	--



Wire Insulation Support	With
-------------------------	------

Dimensions

Wire Size	8233 – 10382 CMA
Stud Diameter	5.3 mm[.209 in]
Tongue Thickness	.8 mm[.031 in]
Product Length	19 mm[.748 in]
Barrel Inside Diameter	2.92 mm, 4.14 mm[.114 in][.162 in]
Compatible Insulation Diameter (Max)	5.31 mm[.209 in]
Compatible Insulation Diameter Range	3.2 – 5.3 mm[.15 – .209 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	5000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 180455-1
TERM PLACA REDONDA 6 DIA.



TE Part # 2150639-1
OCEAN_2.0_APPLICATOR-E-180F250F-REM



TE Part # 2150639-2
OCEAN_2.0_APPLICATOR-E-180F250FA-REA




TE Part # 7-2150639-7
OCEAN_2.0_SPARE_PART_KIT-180F250F




TE Part # 881599-4
RINGUE TONGUE ANTIR

Customers Also Bought



TE Part #1379324-1
52W HYB REC HSG ASSY BLAC



TE Part #1718879-2
RETAINER, 5-6POS. HSG.



TE Part #1544567-3
2POS,NG1 CLIP 8MM,REC HSG, UNSEALED,ASSY



TE Part #1544601-1
PC 1V 8MM NG1 ETANCHABLE





TE Part #953631-1

1W HSG DIESEL GLOW PLUG



TE Part #3-2208804-5

53POS MIXED MQS REC SEALED
COD 3



TE Part #185283-1

SPT WITH BARRIER



TE Part #1801764-1

FUSES AND RELAYS HOLDER, 36
MINIFUSES V2



TE Part #F44439-000

BL-LSTT-6.4-0-30MM

Documents

Product Drawings

RING TONGUE TERMINAL 4.0-6.0 MM2 TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_626036-2_E_c-626036-2-e.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_626036-2_E_c-626036-2-e.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_626036-2_E_c-626036-2-e.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English