

SACC-M12FSB-5CON-PG 7 - Data connector



1453960

<https://www.phoenixcontact.com/us/products/1453960>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Data connector, 5-position, Socket straight M12, coding: B, Screw connection, knurl material: Plastic, cable gland Pg9, external cable diameter 4 mm ... 6 mm

Commercial data

Item number	1453960
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF30
Product key	BF2CAA
GTIN	4046356565202
Weight per piece (including packing)	16.3 g
Weight per piece (excluding packing)	16.3 g
Customs tariff number	85366990
Country of origin	HU

Technical data

Notes

Assembly note

NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.

Product properties

Product type	Circular connector (cable-side)
Number of positions	5
No. of cable outlets	1
Shielded	no
Coding	B
Cable outlet	straight
Pg screw connection	Pg9

Data management status

Article revision	00
------------------	----

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Dimensions

External dimensions

Outside diameter	4 mm ... 6 mm
------------------	---------------

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR
Material of grip body	PA
Contact material	CuZn
Contact surface material	CuSnZn
Contact carrier material	PA
Material for screw connection	Plastic

Connection data

Conductor connection

Connection method	Screw connection
Connection cross section	0.25 mm ² ... 0.75 mm ²
Connection cross section AWG	24 ... 18

Electrical properties

SACC-M12FSB-5CON-PG 7 - Data connector



1453960

<https://www.phoenixcontact.com/us/products/1453960>

Contact resistance	$\leq 8 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	60 V DC
	48 V AC
Nominal current I_N	4 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 50
-----------------------------	-----------

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	B

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 85 °C (Plug)

SACC-M12FSB-5CON-PG 7 - Data connector




1453960

<https://www.phoenixcontact.com/us/products/1453960>

Drawings

Dimensional drawing



M12 x 1 socket, straight

SACC-M12FSB-5CON-PG 7 - Data connector





1453960

<https://www.phoenixcontact.com/us/products/1453960>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1453960>

 cUL Recognized Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	4 A	-	-

 UL Recognized Approval ID: FILE E 221474				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	60 V	4 A	-	-

cULus Recognized				
-------------------------	--	--	--	--

SACC-M12FSB-5CON-PG 7 - Data connector



1453960

<https://www.phoenixcontact.com/us/products/1453960>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2409f725-f01e-4b4e-9898-7e67c69fd627