



Terminals & Splices > Automotive Terminals > TIMER, RECEPTACLE AND TAB



Terminal Type: **Receptacle**
Mating Tab Width: **2.8 mm [.11 in]**
Mating Tab Thickness: **.8 mm [.031 in]**
Terminal Transmits: **0 – 24 A (Low Power)**
Wire Size: **17 – 13 AWG**

[All TIMER, RECEPTACLE AND TAB \(324\)](#)

Features

Product Type Features

Receptacle Style	180°
Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	2.8mm
Contact Fabrication	Stamped & Formed
Typical Current Rating	20 A
Crimp Type	F-Crimp
Terminal Type	Receptacle
Mating Tab Width	2.8 mm[.11 in]
Mating Tab Thickness	.8 mm[.031 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

Compatible Insulation Diameter Range	2.4 – 3.7 mm
--------------------------------------	--------------



Wire Size	1 – 2.5 mm ²
Wire Size Search	13 AWG, 14 AWG, 15 AWG, 16 AWG, 17 AWG

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C [176 °F][185 °F][194 °F][212 °F][221 °F][230 °F]
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Compatible With Agency/Standards Products	IEC 664/664A (DIN VDE 0110)
---	-----------------------------

Packaging Features

Packaging Quantity	3750
Packaging Method	Reel

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-T4827-CH8172 Timer Connector Housing	 TE Part # 2063375-1 SDE JPT 0.5-2.5mm2 ASSY	 TE Part # 2063375-2 SDE JPT 0.5-2.5mm2 DIE SET	 TE Part # 2151245-2 OCEAN_2.0_Applicator-S-110F155F-RSA
 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 7-2151245-7 OCEAN_2.0_SPARE_PART_KIT-110F155F	 TE Part # 720788-8 EXTRCTION TOOL FOR MINI SPRING	 TE Part # 365064-1 8P HSG F/JUNIOR TIMER NAT
 TE Part # 365066-4 14P HSG F/JUNIOR TIMER YLW	 TE Part # 827551-4 2P MI D-FED KONTGEH	 TE Part # 827551-8 2P MI D-FED KONTGEH	

Also in the Series | Timer Connector System



Automotive Connector Caps & Covers
(14)



Automotive Connector Locks &
Position Assurance(15)



Automotive Housings(215)



Automotive Terminals(135)



Connector Seals & Cavity Plugs(38)




Crimp Terminal Housings(13)




Insertion & Extraction Tools(18)



Other Automotive Connector
Accessories(1)



PCB Headers & Receptacles(40)



Quick Disconnects(4)

Customers Also Bought



TE Part #827551-3
JUNIOR TIMER CONNECTOR-HSG



TE Part #284159-1
12 POS. 070 RCPT.HSG. & SEC.LO



TE Part #485043-4
SPLICE 4000-9000 .020 NPST



TE Part #3-2213767-5
AV19 SPL 3A MOVE RING LED GREEN
24V



TE Part #2-2176343-3
CRGCQ 1206 680R 1%



TE Part #1-1419168-2
MARKET 1X6 FEMALE SEALED



TE Part #927833-1
SPT REC 6.3 Contact SRC Sn



TE Part #163307-4
MATE-N-LOK PIN



Documents

Product Drawings

MIN.SPRING RECEPT.

German

CAD Files

Customer View Model

ENG_CVM_925595-1_R1.3d_igs.zip

English

Customer View Model

ENG_CVM_925595-1_R1.3d_stp.zip

English

Customer View Model

ENG_CVM_925595-1_R1.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

German

Application Specification

English

Application Specification

Japanese

CRIMPING L-JETRONIC* MINI-SPRING CONTACT

English

CRIMPING L-JETRONIC* MINI-SPRING CONTACT

Japanese

Application Specification

German

Application Specification

English

925595-1

Receptacle, Mating Tab Width 2.8 mm [.11 in], Tab Thickness .8 mm [.031 in], 17 – 13
AWG Wire Size, Timer Connector System, Automotive Terminals

