





THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1580033~034	2015-07-26	Yulong_wang	Change to Share Drawing.



M 12B - 05 P M M S - S F 8 XXX

12B: B-Code
05: 5Pin
P: Panel (板端)
M: Male Connector (公座)
M: Male Pin (公Pin)
S: Solder Type (焊接式)

001: PG9
002: M16*1.5
8: IP68 (防水等级68)
F: Front Fasten (前锁式/Enclosure Rear Mount)
S: Screw (螺纹式)



Note:

- * Important Dimension.
- * Waterproof Rate: IP68.
- * Housing: Nylon+GF, Black.
- * Male Pin: Copper Alloy, Gold Plated.
- * Shield: Zinc Alloy, Nickel Plated.
- * Screw Nut: Zinc Alloy, Nickel Plated.
- * Panel O-Ring: Viton, Black.
- * Rated Voltage: 60V dc. or ac.
- * Rated Current: 4A
- * Operating Temperature: -40~105°C
- * For Panel Thickness Max 4.5mm.
- * Recommended Nut Torque: 4-6 Kgf.cm.

A	UNIT:mm		TITLE M12 B-Code Male Conn. Solder Front Type			ITEM NO	DRAWN BY Yulong_wang	DATE 2015-07-26
	TOLERANCE		SCALE 2:1	SIZE A4	SHEET 1 OF 1	DWG NO M12B-05PMMS-SF8XXX	CHECKED BY Cary	DATE 2015-07-26
	.X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		REV. B	WC-REV. A.5	QC: Inspection item	CUSTOMER ALTW	APPROVED BY Jerry	DATE 2015-07-26
	Amphenol LTW 安費諾亮泰企業股份有限公司			8 FMW10702-01-02A1				