



MAG-MATE

TE Internal #: 964252-1
Tab, Mating Tab Width 4.75 mm [.187 in], Size 1, .4 – .63 mm
Magnet Wire, 26 – 23 AWG Magnet Wire, MAG-MATE, Magnet
Wire Terminals

[View on TE.com >](#)

Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Tab**
Mating Tab Width: **4.75 mm [.187 in]**
Mating Tab Thickness: **.51 mm, .81 mm [.02 in, .032 in]**
Compatible With Cavity Size: **Size 1**
Magnet Wire Size: **26 – 23 AWG**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire, Solid
------------------------------------	--------------------

Body Features

Compatible With Cavity Size	Size 1
-----------------------------	--------

Contact Features

Magnet Wire Terminal Type	Tab
Mating Tab Width	4.75 mm[.187 in]
Mating Tab Thickness	.51 mm, .81 mm[.02 in][.032 in]
Terminal Plating Material	Tin
Terminal Orientation	Twisted

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Dimensions

Terminal Height	11 mm[.433 in]
-----------------	----------------



Magnet Wire Size	.4 – .63 mm
Stock Thickness (Magnet Wire Side)	.32 mm[.013 in]
Product Length	11 mm[.433 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Quantity	10000
Packaging Method	Reel, Reel/Carton

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1217234-1 MAG-MATE TERM 28-31 013TPBR	TE Part # 964110-1 MAG-MATE KONTAKT	TE Part # 1534234-1 MAG-MATE TAB REC4,8	TE Part # 926851-4 MAG-MATE LEAF KONT
TE Part # 1-928854-1 MAG-MATE FLACHSTECK	TE Part # 1-964106-2 MAG MATE KONTAKT	TE Part # 1-964108-1 MAG-MATE KONTAKT	TE Part # 1217993-1 TAB,187X032 FASTON,MAG-MATE
TE Part # 1418686-1 MAG MATE TERMINAL W.EXTEND. LEAF SPRING	TE Part # 1534110-1 MAG-MATE KONT M.FED	TE Part # 964108-2 MAG-MATE KONTAKT	TE Part # 964111-1 MAG-MATE KONTAKT
TE Part # 969035-1 LACKDRAHTVERBINDER			

Also in the Series | MAG-MATE

Insertion & Extraction Tools(6)	Magnet Wire Terminals(337)	PCB Terminals(1)
--	-----------------------------------	-------------------------



Customers Also Bought

TE Part #1-1394431-1
MAG MATE CONT. 5D

TE Part #964111-1
MAG-MATE KONTAKT

TE Part #964338-5
MAG MATE LEAF KONT

TE Part #2-659667-1
BLADE TRIM, SINGLE

Documents

Product Drawings

MAG-MATE KONTAKT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_964252-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_964252-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_964252-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Magnet Wire Terminals & Splices

English

Product Specifications

Application Specification

English

Instruction Sheets

MAG-MATE CONTACT CAVITY (CONTACT WITH TAB RECEPTACLE 4.8-0.5/0.8)

English

Instruction Sheet (non U.S.)

English