



Connectors > RF Connectors > Coax Connectors > SMB Connector: Male (Jack), Mated Outer Dia. 4.75mm, 50 Ohm



RF Interface: **SMB**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **4.75 mm [.187 in]**

Impedance: **50 Ω**

Compatible With RF Cable Type: **RD 316**

[All SMB Connector: Male \(Jack\), Mated Outer Dia. 4.75mm, 50 Ohm \(2\)](#)

Features

Product Type Features

Connector Product Type	Connector Assembly
RF Interface	SMB
RF Connector Style	Jack
Compatible With RF Cable Type	RD 316
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

--	--



Cable Connector Orientation	Straight
Body Material	Zinc Alloy
Body Plating Material	Nickel

Contact Features

RF Connector Center Contact Underplating Material	Nickel
	50 µin
RF Connector Center Contact Plating Material	Gold
RF Connector Center Contact Material	Brass

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Panel Attachment Style	Rear Mount
RF Connector Coupling Mechanism	Snap-Fit
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	Without

Dimensions

RF Connector Mated Outer Diameter (Approximate)	4.75 mm[.187 in]
---	------------------

Usage Conditions

Operating Temperature Range	-65 – 165 °C[-85 – 329 °F]
-----------------------------	----------------------------

Operation/Application

Operating Frequency	4 GHz
---------------------	-------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Additional Features	Solderless
Grade	Mil-Type
Dielectric Material	PTFE

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------



EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-884-SMBF50
SMB Connector: Plug, Mated Outer Dia. 4.75mm, 50 Ohm

TE Part # CAT-884-SMBV50
SMB Connector: Jack, Vertical Mount, Mated Outer Dia. 4.75mm, 50 Ohm

TE Part # CAT-884-SMBMRA50
SMB Connector: Jack, Right-Angle Mount, Mated Outer Dia. 4.75mm

TE Part # 1-1337478-0
SMB R/A Plg Hex 50Ohm Gold Pla

TE Part # 1060464-1
5164 5003 09

TE Part # 228553-1
SMB COMML BLKHD ADAPTER

TE Part # 414946-1
PLUG ASSY,STR,SMB



Customers Also Bought

TE Part #3-640252-1
Q45 POST CONT 0126PTPBR

TE Part #179609-1
AMP CT CRIMP TTYPE-2 REC CONT.

TE Part #5748271-3
FEMALE SCREWLOCK KIT

TE Part #1-282809-5
TERMI-BLOK PLUG STACKING 4P, M

TE Part #3-747579-0
SHLDNG FERRULE, PLTD, BULK PKG

TE Part #2-87195-4
MOD IV RECP PLTE 15 DPLX

TE Part #292215-6
MINI CT SGL RELAY 6P NAT

TE Part #170452-2
PL 250 AUTOMOTIVE REC 22-20 AWG
PRE TPBR

TE Part #353908-9
CT REC HSG 9P CRIMP TYPE WHITE

Documents

Product Drawings

SMB BLKHD CBL JACK, PB FREE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5415006-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5415006-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5415006-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

5415006-2

SMB RF Interface, Jack, 50 ohm, RD 316, Snap-Fit, 4 GHz Operating Frequency,
Cable-to-Board, 1 Position, Wire & Cable, Panel Mount



Datasheets & Catalog Pages

SMB Connectors

English