




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Board-to-Board**
Number of Positions: **75**
Number of Rows: **3**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stackable	No
PCB Mount Orientation	Vertical
Number of Positions	75
Number of Rows	3

Electrical Characteristics

Insulation Resistance	3 MΩ
-----------------------	------

Body Features

Primary Product Color	Black
-----------------------	-------



Contact Features		
Mating Square Post Dimension		.64 mm[.025 in]
Contact Layout		Matrix
Contact Shape & Form		Four Beam
PCB Contact Termination Area Plating Material		Tin
Contact Base Material		Copper Alloy
Contact Mating Area Plating Material		Gold
		29.9212 µin
Contact Type		Pin
Contact Current Rating (Max)		3 A
Termination Features		
Square Termination Post & Tail Dimension		.64 mm[.025 in]
Termination Post & Tail Length		4.83 mm[.19 in]
Termination Method to PCB		Through Hole - Solder
Mechanical Attachment		
Mating Alignment		Without
PCB Mount Retention		Without
PCB Mount Alignment		Without
Connector Mounting Type		Board Mount
Housing Features		
Centerline (Pitch)		2.54 mm[.1 in]
Housing Material		Thermoplastic
Dimensions		
Connector Height		11.73 mm[.461 in]
Usage Conditions		
Housing Temperature Rating		High
Operating Temperature Range		-65 – 125 °C[-85 – 257 °F]
Operation/Application		
Circuit Application		Signal
Industry Standards		
UL Flammability Rating		UL 94V-0



Packaging Features

Packaging Quantity	7
Packaging Method	Tube

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 532431-1
HDI RECP ASSY 3 ROW 75 POS

TE Part # 5532431-1
ASSY,RECPT,R.ANGLE,HDI,LEAD-FR

Customers Also Bought





TE Part #3-338315-2
25POS.HD20 REC.ASSY



TE Part #3-350820-2
ULTRAFAST 250 ASSY REC 16-14
TPBR LP



TE Part #1623094-1
CRG0603 ZEROHM



TE Part #9148732002
RNF-3000-18/6-9-STK



TE Part #104069-6
40 SYSTEM 50 HDR DRRA SHRD



TE Part #5-1814832-2
SMA Str PCB Skt GZD

Documents

Product Drawings

ASSY,PIN,VERTICAL,HDI,LEAD-FRE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5532433-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5532433-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5532433-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773957-5_AMP_HDI_BTBT_CONNECTORS_EN

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

5532433-1

PCB Mount Header, Vertical, Board-to-Board, 75 Position, 2.54 mm [.1 in] Centerline,
Fully Shrouded, Gold, Through Hole - Solder, Signal, Black, Tube



English