




Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Cable**

Connector Mounting Type: **Cable Mount (Free-Hanging)**

Sealable: **No**

Circuit Application: **Power**

Shell Plating Material: **Electrodeposited Nickel**

Features

Product Type Features

Product Type	Connector Assembly
Connector System	Cable-to-Cable
Sealable	No
Circular Connector Type	Plug
Shell Type	Metal

Electrical Characteristics

Operating Voltage	63 VAC, 630 VAC
-------------------	-----------------

Body Features

Environmental Protection	IP67
Shell Plating Material	Electrodeposited Nickel
Shell Base Material	Zinc Alloy
Circular Connector Insulation Material Type	PBT+PA

Mechanical Attachment

Mating Retention Type	Push-Pull Self-Locking
-----------------------	------------------------

Connector Mounting Type

Cable Mount (Free-Hanging)

Housing Features

Circular Connector Shell Size	15
-------------------------------	----

Dimensions

Cable Diameter Range	4.5 – 6.5 mm[.18 – .26 in]
----------------------	----------------------------

Usage Conditions

Operating Temperature Range	-20 – 130 °C[-4 – 266 °F]
-----------------------------	---------------------------

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Power
Shielded	Yes

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (3.5% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # EGA201N00000800000
915 ITEC RECEPTACLE, ANGLED




TE Part # EKB201N00310500000
915 EXTENSION



TE Part # C0-0258-000-000
POSITIONING INSERT FOR 1 MM CONTACTS




TE Part # C0-0235-000-P00
DIGITAL CRIMPING TOOL, SMALL




TE Part # C0-0201-000-P00
CRIMPING TOOL MID-SIZE


Customers Also Bought




TE Part #AEA874N0000150A000
617 RECEPTACLE, SPEEDTEC-READY




TE Part #ASA021F01620235000
623 PLUG




TE Part #ASA021N00410100000
623 PLUG, SPEEDTEC




TE Part #BSA078N00590100000
923 PLUG, SPEEDTEC




TE Part #ESB002N00310001000
615 PLUG



TE Part #ESB002N00320001000
615 PLUG




TE Part #ESB202N00330500000
915 PLUG



TE Part #AGA139M04001215000
623 receptacle angled rotatable



TE Part #BKA861N0085059A000
917 EXTENSION, SPEEDTEC



TE Part #BSA085N00450235000
923 plug

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_ESB202N00310500000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_ESB202N00310500000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_ESB202N00310500000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ESB202N00310500000

English

915 springtec Plug ESB202N00310500000

English

fuer Datenblaetter, die online konfigurierbar sind

German