




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spring Spade Terminal**

Wire Size: **2050 – 5180 CMA**

Stud Size: **#6, M3.5**

Features

Product Type Features

|                                        |                    |
|----------------------------------------|--------------------|
| Stud Size                              | #6, M3.5           |
| Sealable                               | No                 |
| Wire Insulation Support Retention Type | Insulation Support |

Electrical Characteristics

|                |       |
|----------------|-------|
| Voltage Rating | 600 V |
|----------------|-------|

Body Features

|                         |      |
|-------------------------|------|
| Insulation Sleeve Color | Blue |
| Stripe Color            | Blue |

Contact Features

|                           |                       |
|---------------------------|-----------------------|
| Spade Terminal Type       | Spring Spade Terminal |
| Barrel Type               | Closed                |
| Terminal Orientation      | Straight              |
| Terminal Plating Material | Tin                   |

Mechanical Attachment

|                         |      |
|-------------------------|------|
| Wire Insulation Support | With |
|-------------------------|------|

Dimensions

|                                      |                            |
|--------------------------------------|----------------------------|
| Wire Size                            | 2050 – 5180 CMA            |
| Stud Diameter                        | 3.51 mm[.138 in]           |
| Tongue Thickness                     | .84 mm[.033 in]            |
| Product Length                       | 24 mm[.945 in]             |
| Compatible Insulation Diameter (Max) | 4.9 mm[.193 in]            |
| Compatible Insulation Diameter Range | 3 – 4.9 mm[.118 – .193 in] |

Usage Conditions

|                             |                     |
|-----------------------------|---------------------|
| Insulation Option           | Partially Insulated |
| Operating Temperature Range | 105 °C[221 °F]      |

Operation/Application

|                                       |        |
|---------------------------------------|--------|
| Compatible With Wire Base Material    | Copper |
| Compatible With Wire Plating Material | Tin    |

Industry Standards

|                               |    |
|-------------------------------|----|
| Government Qualified Terminal | No |
|-------------------------------|----|

Packaging Features

|                    |             |
|--------------------|-------------|
| Packaging Quantity | 1000        |
| Packaging Method   | Loose Piece |

Product Compliance

For compliance documentation, visit the product page on TE.com>



|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUNE 2024 (241)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                  |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                                                           |                                                                                                                                          |                                                                                                                                            |                                                                                                                                                           |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 58433-3<br/>PRO CR ASSY, RBY IS9252</p>                   |  <p>TE Part # 59250<br/>T-HEAD PIDG 26-14 ASSY</p>    |  <p>TE Part # 58423-1<br/>DIE, RBY IS9252</p>          |  <p>TE Part # 47387-7<br/>DAHT PG PIDG 16-12 ASSY</p>                 |
|  <p>TE Part # 59824-1<br/>TETRA-CRIMP PIDG PG FASTON 22-10 ASSY</p>    |  <p>TE Part # 47387<br/>DAHT PG PIDG 20-14 ASSY</p>   |  <p>TE Part # 539691-2<br/>ERGO DIE R.B.Y</p>         |  <p>TE Part # 2063030-1<br/>SDE DIESET, RBY, UL</p>                  |
|  <p>TE Part # 47806-2<br/>DIES PIDG 22-16 DIE SET</p>                  |  <p>TE Part # 47807-1<br/>DIES PIDG 16-14 DIE SET</p> |  <p>TE Part # 169400<br/>CERTI-LOK FRAME W/O DIES</p> |  <p>TE Part # 2392022-2<br/>BLUE BATTERY DAHT KIT 220V (47387-7)</p> |
|  <p>TE Part # 2392022-1<br/>BLUE BATTERY DAHT KIT 110V (47387-7)</p> |  <p>TE Part # 169404<br/>CERTI-LOK DIE</p>            |  <p>TE Part # 1SET191001R0000<br/>CRIMP-HT</p>        |  <p>TE Part # 1SET191002R0000<br/>TET CRIMP-HT</p>                   |



Also in the Series | **PLASTI-GRIP**




Compression Connectors(3)



Crimp Wire Pins, Tabs & Ferrules(19)



Ring Terminals(300)



Spade Terminals(160)



Splices(46)

Customers Also Bought



TE Part #2-353908-0  
Mini Common Termination (CT)  
Housings



TE Part #3-640426-7  
07P MTA156 CONN ASSY 18AWG  
ORA



TE Part #794278-1  
09P UMNL WIRE SEAL



TE Part #794276-1  
06P UMNL WIRE SEAL



TE Part #640253-2  
RING TONGUE .190 16-12 AWG TPBR



TE Part #350687-1  
UMNL SPLIT PIN PTPBR



TE Part #ABC03N-16P-4048  
IN-LINE RECP



TE Part #193796-1  
PIN CONTACT - 2MM,10AWG

Documents

Product Drawings  
TERMINAL,PG SPR SPD 16-14 6

English

CAD Files  
3D PDF

3D



Customer View Model  
[ENG\\_CVM\\_CVM\\_52463\\_M.2d\\_dxf.zip](#)  
English

Customer View Model  
[ENG\\_CVM\\_CVM\\_52463\\_M.3d\\_igs.zip](#)  
English

Customer View Model  
[ENG\\_CVM\\_CVM\\_52463\\_M.3d\\_stp.zip](#)  
English

Customer View Model  
[ENG\\_CVM\\_52463\\_J1.3d\\_igs.zip](#)  
English

Customer View Model  
[ENG\\_CVM\\_52463\\_J1.3d\\_stp.zip](#)  
English

Customer View Model  
[ENG\\_CVM\\_52463\\_J1.2d\\_dxf.zip](#)  
English

[3D PDF](#)  
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Product Specifications](#)  
[Application Specification](#)  
English

[Agency Approvals](#)  
[UL Report](#)  
English  
[UL Report](#)  
English