

RN73C1E18K2BTD

✓ ACTIVE

Holsworthy | Holsworthy RN73

TE Internal #: 8-1879132-8

Precision Resistor, Thin Film, 0402, .063 W, 18.2K ohm, .1 %, ±10 ppm/°C, Solder, 2 Termination, Height .3 mm [.012 in], Holsworthy RN73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: Precision Resistor

Element Type: Thin Film

Package Size Code: 0402

Power Rating: .063 W

Resistance Value: 18.2K Ω

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0402

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	25 V
Power Rating	.063 W
Resistance Value	18.2K Ω
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	.1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2



Dimensions

Product Height	.3 mm[.012 in]
Product Length	1 mm[.039 in]
Product Width	.5 mm[.02 in]

Usage Conditions

Temperature Coefficient	±10 ppm/°C
-------------------------	------------

Industry Standards

Moisture Sensitivity Level	1
----------------------------	---

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 8-1879132-6
RN 0402 17K4 0.1% 10PPM 5K RL

TE Part # 8-1879132-9
RN 0402 18K7 0.1% 10PPM 5K RL

Also in the Series | [Holsworthy RN73](#)

Surface Mount Resistors(3788)

Customers Also Bought

TE Part #1625854-3
0603 PROBE PAD

TE Part #8-1879131-7
RN 0402 11K5 0.1% 10PPM 5K RL

TE Part #1676153-3
RN 0805 10K 0.1% 10PPM 5KRL

TE Part #7-1879128-8
RN 0402 1K0 0.1% 10PPM 5K RL

TE Part #6-1879129-6
RN 0402 2K0 0.1% 10PPM 5K RL

TE Part #3-2176263-1
RN 0402 49K9 0.1% 10PPM 5K RL

TE Part #8-1879140-8
RN 0603 150K 0.1% 10PPM 5K RL

Documents

[Product Drawings](#)
[RN 0402 18K2 0.1% 10PPM 5K RL](#)

English

[Datasheets & Catalog Pages](#)

RN73C1E18K2BTD

Precision Resistor, Thin Film, 0402, .063 W, 18.2K ohm, .1 %, ±10 ppm/°C, Solder, 2 Termination, Height .3 mm [.012 in], Holsworthy RN73



High Precision Resistors (SMD) - Type RN73 Series - Tyco Electronics Passives

English