



Connectors > Terminal Blocks & Strips > PCB Terminal Blocks



Terminal Block Connector Type: **Header**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **5 mm [.197 in]**

Number of Rows: **1**

Features

Product Type Features

Header Type	Fully Shrouded
Terminal Block Connector Type	Header
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VAC
-------------------	---------

Body Features

Primary Product Color	Green
Product Orientation	Right Angle

Contact Features

--	--



Contact Mating Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	15 A

Termination Features

Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Mounting Retention Type	Screw Mount, Thread
Connector Mounting Type	Board Mount

Housing Features

Housing Material	PA 66
Centerline (Pitch)	5 mm[.197 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	300
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (.75% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free

Solder Process Capability

Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 284040-2
TERMI-BLOK VERTICAL PLUG STACK




TE Part # 796858-2
2 POS TERMI-BLOK PLUG RT ANGLE




TE Part # 796859-2
2 POS TERMI-BLOK PLUG RT ANGLE



TE Part # 284046-2
TERMI-BLOK VERTICAL PLUG STACK



TE Part # 282805-2
TERMI-BLOK PLUG STACKING 2POS.



TE Part # 796640-2
2 POS 5.0 MM R/A PLUG,TRM BLK

Customers Also Bought



TE Part #2309407-2
DDR4 SODIMM 260P 4.0H STD



TE Part #2324869-2
CONNECTOR ASSY, SMT W
HOLDOWN, PDNI,OSFP



TE Part #5-104068-3
30 SYSTEM 50 HDR DRST SHRD



TE Part #1551576-5
Shield Finger, 3.4mm



TE Part #2338495-5
CAGE ASSEMBLY, 1X4, OSFP

TE Part #5-146280-3
03 MODII HDR SRST B/A .100CL

TE Part #2318579-2
RCPT CONN R/A SMT 76 POSN QSFP-DD WSHRS

TE Part #2358714-1
ICCON BLOCK SIZE 10.3mm PIN

TE Part #364705-E
MSPPM 5 M SMD * 90 A V 137 094 * E008 J

TE Part #6-1393788-1
V23079D1008B301

Documents

Product Drawings

2 POS TERMI-BLOK HDR RT ANGLE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_796864-2_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_796864-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_796864-2_D.3d_stp.zip

English

Customer View Model

ENG_CVM_796864-2_D.3d_igs.zip

English

Customer View Model

ENG_CVM_796864-2_D.3d_stp.zip

English

Customer View Model

ENG_CVM_796864-2_D.2d_dxf.zip

English

3D PDF

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Eurostyle Terminal Blocks Focus Product Stock List

English

BUCHANAN TERMINAL BLOCKS CATALOG - EUROSTYLE TERMINAL BLOCKS

English

BUCHANAN PCB TERMINAL BLOCKS

English

1-1773458-1_EURO_STYLE_TERMINAL_BLOCKS_QRG

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English