



TE Internal #: BKA186N00580200000

Cable-to-Cable, Power & Signal, Cable Mount (Free-Hanging),
Electrodeposited Nickel, Zinc Alloy, PBT GF, Size 23, Standard
Circular Connectors

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Cable-to-Cable**

Connector Mounting Type: **Cable Mount (Free-Hanging)**

Sealable: **No**

Circuit Application: **Power & Signal**

Shell Plating Material: **Electrodeposited Nickel**

Features

Product Type Features

Product Type	Connector Assembly
Connector System	Cable-to-Cable
Sealable	No
Shell Type	Metal

Electrical Characteristics

Operating Voltage	630 VAC
-------------------	---------

Body Features

Environmental Protection	IP67
Shell Plating Material	Electrodeposited Nickel
Shell Base Material	Zinc Alloy
Circular Connector Insulation Material Type	PBT GF

Mechanical Attachment

Mating Retention Type	Speedtec (Triple Start Threaded)
Connector Mounting Type	Cable Mount (Free-Hanging)



Housing Features

Circular Connector Shell Size	23
Alignment Keyed	0°

Dimensions

Cable Diameter Range	9.5 – 14.5 mm[.37 – .57 in]
----------------------	-----------------------------

Usage Conditions

Operating Temperature Range	-20 – 130 °C[-4 – 266 °F]
-----------------------------	---------------------------

Operation/Application

Durability Rating	500 Cycles
Circuit Application	Power & Signal
Shielded	Yes

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (3.5% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # BSA085N00580235000
923 PLUG



TE Part # C0-0004-000-000
POSITIONING INSERT FOR 2 MM CONTACTS




TE Part # C0-0009-000-000
POSITIONING INSERT FOR 2 MM CONTACTS


TE Part # C0-0201-000-P00
CRIMPING TOOL MID-SIZE

TE Part # C0-0236-000-P00
DIGITAL CRIMPING TOOL, MID SIZE


Customers Also Bought




TE Part #AKA000N00620200000
623 EXTENSION, SPEEDTEC-READY




TE Part #ASA384N0055001K000
627 PLUG, 26-PIN




TE Part #BSA078N00420235000
923 PLUG




TE Part #BSA078N00580100000
923 PLUG, SPEEDTEC



TE Part #BSA078N00580235000
923 PLUG



TE Part #ESA202N00340500000
915 PLUG



TE Part #AKA000N00610200000
623 EXTENSION, SPEEDTEC-READY

TE Part #40-0623-000-000
623 INSULATION INSERT, 17-PIN



Documents

Product Drawings

923 EXTENSION, SPEEDTEC-READY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_BKA186N00580200000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_BKA186N00580200000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_BKA186N00580200000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BKA186N00580200000

English

fuer Datenblaetter, die online konfigurierbar sind

German

Product Specifications

German