



Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Split Ring Ferrule**
Primary Product Material: **Composite**
Operating Temperature Range: **-65 – 175 °C [-85 – 347 °F]**

Features

Product Type Features

Strain Relief Accessory Type	Split Ring Ferrule
------------------------------	--------------------

Body Features

Primary Product Material	Composite
--------------------------	-----------

Dimensions

Product Length	22.35 mm[.88 in]
----------------	------------------

Usage Conditions

Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]
-----------------------------	----------------------------

Industry Standards

Compatible With Approved Standards Products	85049/93
---	----------

Other

Entry Size Code	14
-----------------	----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224)




	Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Split Banding Ring



Connector Strain Relief(16)

Customers Also Bought



TE Part #576778
HHHT PIDG PEEK STRATO 24-22 ASSY



TE Part #206800-2
PLG ASSY,25 POS,AMPLIMITE



TE Part #4-643819-2
12P MTA156 CONN ASSY 22AWG LF



TE Part #2176403-7
3550 1R8 1%





TE Part #169311-000
[55A1822-24-9/96-9CS2275](#)



TE Part #EM6342-000
[R85049/93-06](#)



TE Part #EM6343-000
[R85049/93-08](#)

TE Part #YCTJ122E10AC015000
[ELEC MODULE](#)



TE Part #YDTS24G19-11PAV001
[RECP ASSY](#)

Documents

Product Drawings

[R85049/93-14](#)

English