

MULTI-BEAM

TE Internal #: 1600798-7

Housing, Receptacle, Cable-to-Board / Cable-to-Panel, 2 Position,
7.62 mm [.3 in] Centerline, Printed Circuit Board, Rectangular Power
Connectors

[View on TE.com >](#)



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Cable-to-Board, Cable-to-Panel**

Number of Positions: **2**

Centerline (Pitch): **7.62 mm [.3 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board, Cable-to-Panel
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	300 VDC
-------------------	---------

Contact Features

Power Contact Base Material	Tin
Contact Retention Within Housing	Without
Contact Type	Receptacle



Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

PCB Mount Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	7.62 mm[.3 in]
Housing Color	Black
Housing Material	Thermoplastic

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Method	Tube
------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 6600383-1
MBXL VERT HDR 6P+32S+6P STR

Customers Also Bought

TE Part #1648203-1
297-08-01100=SA CONN,PIN

TE Part #5747100-3
CABLE CLAMP KIT,SZ 4

TE Part #5569260-1
STK MJ ASSY,8POS,2X2,SHLD,CAT5

TE Part #5650906-5
ASSY,PIN,EUROCARD,TYPE C,LEAD-

TE Part #5535043-4
ASSY,RECEPTACLE,EUROCARD,TYPE

TE Part #745245-2
SPECIAL LATCH BLOCK-2 PER BAG

TE Part #5530843-7
CONN SEC II 30 POS 100C/L

TE Part #2-34152-2
PG R 22-16 COMM 22-18 MIL 3/8



TE Part #5535098-5
ASSEMBLY,RECEPTACLE,EUROCARD,
T



TE Part #5536501-2
2MM FB,ASY,48,SIG,HDR,SL,4.25

Documents

Product Drawings

STR RCPT ASSY MBXL W/KEYS 2ACP

English

CAD Files

Customer View Model

ENG_CVM_CVM_1600798-7_F1.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1600798-7_F1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1600798-7_F1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

2_PIECE_POWER_CONNECTORS_qrg_4-1773458-1

English

Product Specifications

Application Specification

English