

HPP845E131R4

✓ ACTIVE

MEAS | MEAS HTU

TE Internal #: HPP845E131R4


TE Internal Description: HTU21DF RH/T SENSOR IC B400

HTU21D Digital High Accuracy RH/T Sensor

[View on TE.com >](#)



Sensors > Humidity Sensors > Humidity Sensor Components > HTU21D Digital High Accuracy RH/T Sensor



Humidity Sensor Product Type: RHT
Supply Voltage (Peak): 3.8 V
Current Consumption: .014 mA
Operating Temperature Range: -40 – 125 °C [-40 – 257 °F]
Interface Signal Type: Digital

[All HTU21D Digital High Accuracy RH/T Sensor \(4\)](#)

Features

Product Type Features

Humidity Sensor Product Type	RHT
Interface Signal Type	Digital

Electrical Characteristics

Supply Voltage (Peak)	3.8 V
Current Consumption	.014 mA

Usage Conditions

Humidity Operating Range	0 – 100 %RH
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2023 (235)



Does not contain REACH SVHC

Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-HSC0004
HTU21D Digital High Accuracy RH/T Sensor



TE Part # HPP845E132R4
I.C 21PF RH/T PWM B400

Also in the Series | MEAS HTU



Humidity Sensor Assemblies(4)



Humidity Sensor Components(18)




Sensor Development Boards and Evaluation Kits(3)

Customers Also Bought




TE Part #1534238-1
MESSERLEISTE 21P



TE Part #1-1393258-5
V23047-A1024-A501



TE Part #7-338069-4
MICRO-MATCH SMD FTE



TE Part #215297-7
7P HV100 REC CON. TE, 7.0MM




TE Part #5650895-4
ASSY,RECEPT,EUROCARD,TYPE R,LE




TE Part #2213189-3
Assembly, IPI Connector 22-18GA w
cap



TE Part #2176186-1
CRGH1206 1% 120R 0.5W



TE Part #5-2176452-6
CPF 0201 2K0 0.1% 25ppm 1K RL



TE Part #2176451-1
CPF 0201 49R9 0.1% 25ppm 1K RL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_HPP845E131R4_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_HPP845E131R4_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_HPP845E131R4_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HTU21D

English

HTU21A(F) data sheet

English

