



Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**

PCB Thickness (Recommended): **1.57 mm [.062 in]**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

PCB Hole Diameter: **2.54 mm [.1 in]**

Features

Contact Features

PCB Contact Termination Area Plating Material Thickness	3.81 μm[150 μin]
Contact Underplating Material Thickness	2.54 μm[100 μin]
Contact Mating Area Plating Material Thickness	3.81 μm[150 μin]
PCB Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Plating Material	Tin
Contact Underplating Material	Brass
Terminal Size	6.35
Terminal Orientation	Straight

Termination Features

Termination Method to PCB	Through Hole - Solder
Product Terminates To	Printed Circuit Board

Mechanical Attachment



Wire Insulation Support	With
-------------------------	------

Dimensions

Extension Below Board	3.69 mm[.145 in]
Terminal Material Thickness	.81 mm[.032 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]
PCB Hole Diameter	2.54 mm[.1 in]
Profile Height from PCB	12.06 mm[.48 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 735427-2 110 FASTON TAB TPBR	 TE Part # 1217169-1 250 FASTON,PCB TAB,TCBR	 TE Part # 61134-3 110 FASTON TAB TPBR	 TE Part # 62409-1 250 FASTON TAB TPBR
 TE Part # 1217057-1 187 FASTON,PCB TAB,TPBR	 TE Part # 1217167-1 250 FASTON,PCB TAB,TCBR	 TE Part # 1217056-1 250 FASTON,PCB TAB,TPBR	 TE Part # 63849-1 250 FASTON TAB TPBR
 TE Part # 63900-1 250 FASTON TAB TPBR	 TE Part # 1742686-1 250 FASTON,PCB TAB,TCBR	 TE Part # 1217754-1 250 FASTON,FLAG,PCB TAB,TNBR	 TE Part # 62262-1 250 FASTON TAB TPBR
 TE Part # 1217421-1 250 FASTON,PCB TAB,TNBR	 TE Part # 63849-4 250 FASTON TAB SPBR		

Also in the Series | FASTON 250



 Compression Connectors(4)	 Crimp Terminal Housings(132)	 Insertion & Extraction Tools(6)	 Magnet Wire Terminals(1)
 PCB Terminals(134)	 Quick Disconnects(426)	 Splices(4)	

Customers Also Bought

 TE Part #2-5747706-0 09 RCPT SP/FMS BRDLK	 TE Part #1-2040516-5 DYNAMIC 1100D HDR ASSY V 10PX BLACK GOLD	 TE Part #2-178136-2 DYNAMIC D3200 HDR V ASSY 3P	 TE Part #3-641217-8 08P MTA156 CONN ASSY 18AWG ORA
 TE Part #6648318-1 CONTACT,SKT,#12	 TE Part #DTP13-4P HDR, 4P, BLK, RA, SN/NI/CU	 TE Part #1650153-2 701-12-02109=CONTACT,PIN,#12	 TE Part #1648128-1 235-0153-01100=SKT,MARKED

Documents

Product Drawings
250 FASTON TAB TPBR

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_63067-1_L_c-63067-1-l.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_63067-1_L_c-63067-1-l.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63067-1_L_c-63067-1-l.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON PCB Tabs and Receptacles](#)

English

[PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[CSA Certificate](#)

English

[CSA Certificate](#)

English