




Connectors > Connector Accessories > Connector Backshells



Primary Product Material: PBT

Operating Temperature Range: -40 – 125 °C [-40 – 257 °F]

Features

Body Features

Cable Exit Angle	180°
Primary Product Color	Black
Primary Product Material	PBT

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.





Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 9-2367337-3 2POS,CSS SIZE 20,SOC OUTER HSG ASSY,SLD	 TE Part # 9-2367346-1 SWS,HSD,CVTY DIA,RECTANGULAR	 TE Part # 9-2367337-1 2POS,CSS SIZE 20,SOC OUTER HSG ASSY,SLD	 TE Part # 9-2367337-2 2POS,CSS SIZE 20,SOC OUTER HSG ASSY,SLD
 TE Part # 9-2367337-4 2POS,CSS SIZE 20,SOC OUTER HSG ASSY,SLD	 TE Part # 9-2367344-3 PIN CONN CVR,2POS,CSS SIZE 20,180 DEG	 TE Part # 9-2367346-2 SWS,HSD,CVTY DIA,RECTANGULAR	

Also in the Series | DEUTSCH DT Highspeed

 Automotive Connector EMC Shielding (5)	 Automotive Housings(2)	 Connector Backshells(2)	 Connector Seals & Cavity Plugs(2)
---	--	--	--



Data Connectivity Housings(1)



Infotainment & Multimedia Cable Assemblies(15)



Other Automotive Connector Accessories(6)



PCB Headers & Receptacles(3)

Customers Also Bought



TE Part #1011-345-0305
DUST CAP, 3P, PLG, BLK, DT



TE Part #2384003-1
BLIND CONNECTOR,REC HSG ASSY, DATA DT



TE Part #9-2367346-1
SWS,HSD,CVTY DIA,RECTANGULAR



TE Part #9-2370624-1
CU ALLOY,OUTER FERRULE,DATA DT



TE Part #2292860-2
AS16,CAP BACKSHELL KIT,ST,02P, NC12



TE Part #YHDP24-24-31PEL024
REC, 31P, BLK, E, WTHD, 16, P



TE Part #9-2367337-1
2POS,CSS SIZE 20,SOC OUTER HSG ASSY,SLD



TE Part #9-2367341-1
2POS,CSS SIZE 20,PIN OUTER HSG ASSY



TE Part #9-2367344-1
PIN CONN CVR,2POS,CSS SIZE 20,180 DEG



TE Part #9-2367344-3
PIN CONN CVR,2POS,CSS SIZE 20,180 DEG

Documents

Product Drawings

SOC CONN CVR ASSY,2POS,CSS SIZE 20,180

English

CAD Files

Customer View Model

ENG_CVM_CVM_9-2367345-1_C1.2d_dxf.zip

English

Customer View Model



[ENG_CVM_CVM_9-2367345-1_C1.3d_igs.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_9-2367345-1_C1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Product Specifications](#)

[Application Specification](#)

English