




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 2582 – 6529 CMA

Stud Size: #8, M4

Features

Product Type Features

Shape Description	Anti-Rotational/Grounding
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#8, M4
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Contact Base Material	Brass
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin
Contact Underplating Material	Nickel

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.13 in
--	--------



Wire Size	2582 – 6529 CMA
Stud Diameter	4.39 mm[.172 in]
Tongue Thickness	.76 mm[.03 in]
Product Length	19.56 mm[.77 in]
Barrel Inside Diameter	2.03 mm, 3.93 mm[.08 in][.155 in]
Compatible Insulation Diameter (Max)	4.32 mm[.17 in]
Compatible Insulation Diameter Range	3.3 – 4.32 mm[.13 – .17 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	6000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2150653-1
[OCEAN_2.0_APPLICATOR-E-140F220O-REM](#)

TE Part # 2150653-2
[OCEAN_2.0_APPLICATOR-E-140F220OA-REA](#)

TE Part # 7-2150653-7
[OCEAN_2.0_SPARE_PART_KIT-140F220O](#)

Customers Also Bought

TE Part #2-2176231-3
[3522 82R 1% 3W](#)

TE Part #1-5103308-0
[A/L LOW PRO HDR 50P VERT BLACK](#)

TE Part #3-520412-2
[ULTRA-FAST 187 ASY REC 16-14 AWG TPBR](#)

TE Part #2-521102-2
[ULTRA-FAST 187 ASY Tab 22-18 TPBR](#)

TE Part #60799-5
[SHUR PLUG 180 RECEPTACLE 18-14 AWG TPBR](#)

TE Part #62253-2
[250 FASTON REC 14-10 TPBR](#)

TE Part #42742-2
[250 FASTON FLAG REC 18-12 AWG TPBR](#)

TE Part #737440-2
[250 FASTON REC 17-14 AWG TPBR](#)

TE Part #282836-2
[TERMI-BLOK PCB MOUNT 90 2P.](#)

TE Part #5-1814832-2
[SMA Str PCB Skt GZD](#)



Documents

Product Drawings

FASTON .187 (4.75 MM) ADAPTER TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63698-1_C_c-63698-1-c.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_63698-1_C_c-63698-1-c.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63698-1_C_c-63698-1-c.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

EB**General Application Specification for Open Barrel Terminals

English

Application Specification

English

Application Specification

English