

RF Power Pot Capacitors With Mounting Tags, Class 1 Ceramic



FEATURES

- Small size
- High reliability
- Wide range of capacitance values

APPLICATIONS

- Induction and dielectric heating
- Antenna units
- Filter, bypass, and coupling circuits

QUICK REFERENCE DATA							
DESCRIPTION	VALUE						
Ceramic class	1						
Ceramic dielectric	R7, R16, R42, R85						
Type	TD 020030			TD 020050		TD 020080	
Voltage (V _p)	6000	7000	8000	7000	8000	7000	8000
Min. capacitance (pF)	100	80	10	200	20	1200	40
Max. capacitance (pF)	400	250	160	600	500	1200	1000
Mounting	Screw terminal						

MATERIAL

Capacitor elements made from class 1 ceramic dielectric with noble metal electrodes.

Connection terminals:
made from copper / brass, silver plated.

FINISH

Capacitor body completely protective lacquered.
The contoured insulating rim is additionally glazed.

MARKING

Type designator, capacitance value and tolerance, rated peak voltage, ceramic material code, production date code, manufacturer logo.

CAPACITANCE RANGE

10 pF to 1.2 nF

CAPACITANCE TOLERANCE

± 20 %; ± 10 %; ± 5 %

DIELECTRIC STRENGTH TEST

200 % of rated AC voltage (50 Hz, 5 minutes)

CERAMIC DIELECTRICS

- R7 (TCC + 100 ppm/K)
- R16 (TCC + 100 ppm/K)
- R42 (TCC - 250 ppm/K)
- R85 (TCC - 750 ppm/K)

RATED VOLTAGE

- 6.0 kV_p
- 7.0 kV_p
- 8.0 kV_p

DISSIPATION FACTOR

R7: max. 0.07 %
R16: max. 0.04 %
R42, R85: max. 0.05 %

Measuring frequencies:
1 MHz (< 1 nF); 300 kHz or 100 kHz (≥ 1 nF)

INSULATION RESISTANCE

Min. 100 000 MΩ (at 25 °C)

OPERATING TEMPERATURE RANGE


-55 °C to +100 °C









SAP PART NUMBER AND ELECTRICAL DATA					
PART NUMBER	CERAMIC	CAP. VALUES (pF)	RATED VOLTAGE (kV _p)	RATED POWER ⁽¹⁾ (kvar)	RATED CURRENT (A _{RMS})
TYPE TD 020030					
TD020030BP100##BF1	R7	10	8.0	3.5	6.0
TD020030BP160##BF1		16			
TD020030BP200##BF1		20			
TD020030BP250##BG1	R16	25		4.2	
TD020030BP400##BG1		40			
TD020030BP500##BH1	R42	50			
TD020030BP600##BH1		60			
TD020030VY800##BH1		80	7.0		
TD020030BF101##BH1		100	6.0		
TD020030BP121##BJ1	R85	120	8.0		
TD020030BP161##BJ1		160	7.0		
TD020030VY201##BJ1		200			
TD020030VY251##BJ1		250	6.0		
TD020030BF301##BJ1		300			
TD020030BF401##BJ1		400			
TYPE TD 020050					
TD020050BP200##BF1	R7	20	8.0	5.6	6.0
TD020050BP250##BF1		25			
TD020050BP400##BG1	R16	40			
TD020050BP500##BG1		50		7.0	
TD020050BP600##BG1		60			
TD020050BP800##BG1		80			
TD020050BP101##BH1	R42	100			
TD020050BP161##BH1		160	7.0		
TD020050VY201##BH1		200			
TD020050BP251##BJ1	R85	250	8.0		
TD020050BP301##BJ1		300			
TD020050BP401##BJ1		400			
TD020050BP501##BJ1		500			
TD020050VY601##BJ1		600	7.0		
TYPE TD 020080					
TD020080BP400##BF1	R7	40	8.0	8.5	7.0
TD020080BP600##BF1		60			
TD020080BP800##BG1	R16	80			
TD020080BP101##BG1		100		10.5	
TD020080BP121##BG1		120			
TD020080BP161##BG1		160			
TD020080BP201##BH1	R42	200			
TD020080BP251##BH1		250			
TD020080BP301##BH1		300			
TD020080BP401##BJ1	R85	400			
TD020080BP501##BJ1		500			
TD020080BP601##BJ1		600			
TD020080BP102##BJ1		1000			
TD020080VY122##BJ1		1200	7.0		









Notes









- ## 14th to 15th digit: capacitance tolerance code $\pm 20\% = 38$, $\pm 10\% = 36$, $\pm 5\% = 33$
- (1) The surface temperature during operation must not exceed +100 °C









DIMENSIONS in millimeters (inches)










TYPE	TD 020030	TD 020050	TD 020080
Length L	36 (1.42)	56 (2.20)	86 (3.39)






DERATING DIAGRAMS
TD020030BP100##BF1

TD020030BP160##BF1

TD020030BP200##BF1

TD020030BP250##BG1

TD020030BP400##BG1

TD020030BP500##BH1


DERATING DIAGRAMS
TD020030BP600##BH1

TD020030VY800##BH1

TD020030BF101##BH1

TD020030BP121##BJ1

TD020030BP161##BJ1

TD020030VY201##BJ1

TD020030VY251##BJ1

TD020030BF301##BJ1


DERATING DIAGRAMS
TD020030BF401##BJ1

TD020050BP200##BF1

TD020050BP250##BF1

TD020050BP400##BG1

TD020050BP500##BG1

TD020050BP600##BG1

TD020050BP800##BG1

TD020050BP101##BH1


DERATING DIAGRAMS
TD020050BP161##BH1

TD020050VY201##BH1

TD020050BP251##BJ1

TD020050BP301##BJ1

TD020050BP401##BJ1

TD020050BP501##BJ1

TD020050VY601##BJ1

TD020080BP400##BF1


DERATING DIAGRAMS
TD020080BP600##BF1

TD020080BP800##BG1

TD020080BP101##BG1

TD020080BP121##BG1

TD020080BP161##BG1

TD020080BP201##BH1

TD020080BP251##BH1

TD020080BP301##BH1


DERATING DIAGRAMS
TD020080BP401##BJ1

TD020080BP501##BJ1

TD020080BP601##BJ1

TD020080BP102##BJ1

TD020080VY122##BJ1

RELATED DOCUMENTS

General Information

www.vishay.com/doc?22071



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.